



REVISIONS				
P	LTN	DESCRIPTION	DATE	OWN APVD
L		REVISED PER ECO-19-012453	13AUG2019	AP GF
M		REVISED AS PER ECN-21-132059	22DEC2021	KK AK
N		REVISED AS PER ECN-23-197955	08FEB2023	MT GL
N1		REVISED AS PER ECN-24-252801	20FEB2024	JK GL




1 LABEL INFORMATION: -1 SHOWN.



- SEE SHEET 2 FOR WIRING SCHEMATIC.
- PRODUCT AND PROCESSING MUST MEET THE REQUIREMENTS OF TE SPECIFICATION TEC-138-702. (CONTAINS NO BANNED OR RESTRICTED SUBSTANCES)
- EEPROM DOES NOT INCLUDE PAGE SWAPPING.
- TEST IN ACCORDANCE WITH IEEE802.3bj.

6 DUE TO SHORT CABLE LENGTH, THE PART NUMBERS INDICATED MAY NOT MEET IEEE802.3bj. RETURN LOSS AND MINIMUM INSERTION LOSS LIMITS


7 CE MARKING LABEL INFORMATION (EXAMPLE SHOWS CHINA AND MEXICO MANUFACTURING ADDRESS):



STATUS	PART NO.	LENGTH (mm)	PLC	DATE	PART NO.
OBSOLETE		30	3500 +80/-0		3-2231368-5
	4WZ6Y2	30	2500 +80/-0		3-2231368-4
SUPERSEDED BY 2333842-5		26	2500 +80/-0		3-2231368-3
	4WZ6XR	30	500 +50/-0		2-2231368-3
SUPERSEDED BY 2336313-1		33	500 +50/-0		2-2231368-2
SUPERSEDED BY 2333841-8		28	4000 +80/-0		2-2231368-1
SUPERSEDED BY 2333841-4		28	2000 +80/-0		2-2231368-0
OBSOLETE		24	7000 +100/-0		1-2231368-9
SUPERSEDED BY 2336313-4		33	2000 +80/-0		1-2231368-8
SUPERSEDED BY 2336313-3		33	1500 +50/-0		1-2231368-7
SUPERSEDED BY 2336313-2		33	1000 +50/-0		1-2231368-6
SUPERSEDED BY 2333842-3		26	1500 +50/-0		1-2231368-5
SUPERSEDED BY 2333842-4		26	2000 +80/-0		1-2231368-4
OBSOLETE		30	4000 +80/-0		1-2231368-3
SUPERSEDED BY 1-2333842-0		26	5000 +80/-0		1-2231368-2
OBSOLETE		24	4000 +80/-0		1-2231368-1
OBSOLETE		24	3000 +80/-0		1-2231368-0
	4WZ6XB	30	1500 +50/-0		2231368-9
	4WZ6XA	30	3000 +80/-0		2231368-8
SUPERSEDED BY 2333842-6		26	3000 +80/-0		2231368-7
OBSOLETE		24	6000 +80/-0		2231368-6
OBSOLETE		24	5000 +80/-0		2231368-5
SUPERSEDED BY 2333842-8		26	4000 +80/-0		2231368-4
SUPERSEDED BY 2333841-6		28	3000 +80/-0		2231368-3
	4WZ6X4	30	2000 +80/-0		2231368-2
	4WZ6X3	30	1000 +50/-0		2231368-1
	'PPPPPP' SN PREFIX	GAGE	"L" mm		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT. OWN: T. SMITH 08FEB2017. CHK: E. CUESTA 08FEB2017. APVD: E. CUESTA 08FEB2017. NAME: CABLE ASSEMBLY, DIRECT ATTACH QSFP 25GIG. DIMENSIONS: mm. TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±, 1 PLC ±, 2 PLC ±, 3 PLC ±, 4 PLC ±, ANGLES ±, FINISH ±. MATERIAL: -. WEIGHT: -. CUSTOMER DRAWING. SCALE: 7:5. SHEET 1 OF 2. REV: N1.

REVISIONS				
P	LTN	DESCRIPTION	DATE	APVD
-	SEE SHEET 1			



WIRING PATTERN

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN T. SMITH 08FEB2017	
		CHK E. CUESTA 08FEB2017	
DIMENSIONS:		APVD E. CUESTA 08FEB2017	NAME CABLE ASSEMBLY, DIRECT ATTACH QSFP 25GIG
mm		PRODUCT SPEC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	RESTRICTED TO
0 PLC ±		SIZE A1	SCALE 6:5 SHEET 2 OF 2 REV N1
1 PLC ±		CAGE CODE -	
2 PLC ±		DRAWING NO. C=2231368	
3 PLC ±		WEIGHT -	
4 PLC ±		CUSTOMER DRAWING	
ANGLES ±			
FINISH ±			