



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1		REVISED PER ECN-24-247111	02FEB2024	RK	CAS



- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 2 TRUE POSITION TOLERANCE OF POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 3 0.00076[.000030] MIN GOLD ON CONTACT AREA, MATTE TIN ON SOLDER AREA, ALL OVER 0.00127[.000050] NICKEL.
- 4 0.00007[.000003] MIN GOLD OVER 0.00068[.000027] Pd/Ni ON CONTACT AREA, MATTE TIN ON SOLDER AREA, ALL OVER 0.00127[.000050] NICKEL.
- 5 MATERIAL:
HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK.
POSTS: PHOS BRONZE.
- 6 PRELIMINARY PART NUMBER NOT RELEASED FOR PRODUCTION.



RECOMMENDED HOLE LAYOUT

FINISH	C	B	A	NO OF POSN	PART NUMBER	
OBSOLETE	3	101.19 [3.984]	99.06 [3.900]	39	40	4-2267061-0
6	3	98.65 [3.884]	96.52 [3.800]	38	39	3-2267061-9
6	3	96.11 [3.784]	93.98 [3.700]	37	38	3-2267061-8
6	3	93.57 [3.684]	91.44 [3.600]	36	37	3-2267061-7
6	3	91.03 [3.584]	88.90 [3.500]	35	36	3-2267061-6
6	3	88.49 [3.484]	86.36 [3.400]	34	35	3-2267061-5
6	3	85.95 [3.384]	83.82 [3.300]	33	34	3-2267061-4
6	3	83.41 [3.284]	81.28 [3.200]	32	33	3-2267061-3
6	3	80.87 [3.184]	78.74 [3.100]	31	32	3-2267061-2
6	3	78.33 [3.084]	76.20 [3.000]	30	31	3-2267061-1
6	3	75.79 [2.984]	73.66 [2.900]	29	30	3-2267061-0
6	3	73.25 [2.884]	71.12 [2.800]	28	29	2-2267061-9
6	3	70.71 [2.784]	68.58 [2.700]	27	28	2-2267061-8
6	3	68.17 [2.684]	66.04 [2.600]	26	27	2-2267061-7
6	3	65.63 [2.584]	63.50 [2.500]	25	26	2-2267061-6
6	3	63.09 [2.484]	60.96 [2.400]	24	25	2-2267061-5
6	3	60.55 [2.384]	58.42 [2.300]	23	24	2-2267061-4
6	3	58.01 [2.284]	55.88 [2.200]	22	23	2-2267061-3
6	3	55.47 [2.184]	53.34 [2.100]	21	22	2-2267061-2
6	3	52.93 [2.084]	50.80 [2.000]	20	21	2-2267061-1
OBSOLETE	3	50.39 [1.984]	48.26 [1.900]	19	20	2-2267061-0
6	3	47.85 [1.884]	45.72 [1.800]	18	19	1-2267061-9
OBSOLETE	3	45.31 [1.784]	43.18 [1.700]	17	18	1-2267061-8
OBSOLETE	3	42.77 [1.684]	40.64 [1.600]	16	17	1-2267061-7
OBSOLETE	3	40.23 [1.584]	38.10 [1.500]	15	16	1-2267061-6
OBSOLETE	3	37.69 [1.484]	35.56 [1.400]	14	15	1-2267061-5
OBSOLETE	3	35.15 [1.384]	33.02 [1.300]	13	14	1-2267061-4
OBSOLETE	3	32.61 [1.284]	30.48 [1.200]	12	13	1-2267061-3
OBSOLETE	3	30.07 [1.184]	27.94 [1.100]	11	12	1-2267061-2
OBSOLETE	3	27.53 [1.084]	25.40 [1.000]	10	11	1-2267061-1
OBSOLETE	3	24.99 [.984]	22.86 [.900]	9	10	1-2267061-0
OBSOLETE	3	22.45 [.884]	20.32 [.800]	8	9	2267061-9
OBSOLETE	3	19.91 [.784]	17.78 [.700]	7	8	2267061-8
OBSOLETE	3	17.37 [.684]	15.24 [.600]	6	7	2267061-7
OBSOLETE	3	14.83 [.584]	12.70 [.500]	5	6	2267061-6
OBSOLETE	3	12.29 [.484]	10.16 [.400]	4	5	2267061-5
OBSOLETE	3	9.75 [.384]	7.62 [.300]	3	4	2267061-4
OBSOLETE	3	7.21 [.284]	5.08 [.200]	2	3	2267061-3
OBSOLETE	3	4.67 [.184]	2.54 [.100]	1	2	2267061-2
OBSOLETE	3	2.13 [.084]	-	-	1	2267061-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: 03FEB2014 NAGALAKSHMI K
CHK: 03FEB2014 MILLER MICHAEL
APVD: 03FEB2014 MILLER MICHAEL

TE Connectivity Ltd.

ASSY, MOD II, HEADER, SINGLE ROW, 2.54[.100]C/L VERTICAL, 0.64[.025] SQ POSTS

SIZE: A2 CAGE CODE: 00779 DRAWING NO: C=2267061 RESTRICTED TO: -

SCALE: 4:1 SHEET: 1 OF 2 REV: A1


MATERIAL: 5 FINISH: POSTS: 3

PRODUCT SPEC: - APPLICATION SPEC: - WEIGHT: - CUSTOMER DRAWING

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

OBSOLETE	△ ₄	101.19 [3.984]	99.06 [3.900]	39	40	9-2267061-0
△ ₆	△ ₄	98.65 [3.884]	96.52 [3.800]	38	39	8-2267061-9
△ ₆	△ ₄	96.11 [3.784]	93.98 [3.700]	37	38	8-2267061-8
△ ₆	△ ₄	93.57 [3.684]	91.44 [3.600]	36	37	8-2267061-7
△ ₆	△ ₄	91.03 [3.584]	88.90 [3.500]	35	36	8-2267061-6
△ ₆	△ ₄	88.49 [3.484]	86.36 [3.400]	34	35	8-2267061-5
△ ₆	△ ₄	85.95 [3.384]	83.82 [3.300]	33	34	8-2267061-4
△ ₆	△ ₄	83.41 [3.284]	81.28 [3.200]	32	33	8-2267061-3
△ ₆	△ ₄	80.87 [3.184]	78.74 [3.100]	31	32	8-2267061-2
△ ₆	△ ₄	78.33 [3.084]	76.20 [3.000]	30	31	8-2267061-1
△ ₆	△ ₄	75.79 [2.984]	73.66 [2.900]	29	30	8-2267061-0
△ ₆	△ ₄	73.25 [2.884]	71.12 [2.800]	28	29	7-2267061-9
△ ₆	△ ₄	70.71 [2.784]	68.58 [2.700]	27	28	7-2267061-8
△ ₆	△ ₄	68.17 [2.684]	66.04 [2.600]	26	27	7-2267061-7
△ ₆	△ ₄	65.63 [2.584]	63.50 [2.500]	25	26	7-2267061-6
△ ₆	△ ₄	63.09 [2.484]	60.96 [2.400]	24	25	7-2267061-5
△ ₆	△ ₄	60.55 [2.384]	58.42 [2.300]	23	24	7-2267061-4
△ ₆	△ ₄	58.01 [2.284]	55.88 [2.200]	22	23	7-2267061-3
△ ₆	△ ₄	55.47 [2.184]	53.34 [2.100]	21	22	7-2267061-2
△ ₆	△ ₄	52.93 [2.084]	50.80 [2.000]	20	21	7-2267061-1
OBSOLETE	△ ₄	50.39 [1.984]	48.26 [1.900]	19	20	7-2267061-0
△ ₆	△ ₄	47.85 [1.884]	45.72 [1.800]	18	19	6-2267061-9
OBSOLETE	△ ₄	45.31 [1.784]	43.18 [1.700]	17	18	6-2267061-8
OBSOLETE	△ ₄	42.77 [1.684]	40.64 [1.600]	16	17	6-2267061-7
OBSOLETE	△ ₄	40.23 [1.584]	38.10 [1.500]	15	16	6-2267061-6
OBSOLETE	△ ₄	37.69 [1.484]	35.56 [1.400]	14	15	6-2267061-5
OBSOLETE	△ ₄	35.15 [1.384]	33.02 [1.300]	13	14	6-2267061-4
OBSOLETE	△ ₄	32.61 [1.284]	30.48 [1.200]	12	13	6-2267061-3
OBSOLETE	△ ₄	30.07 [1.184]	27.94 [1.100]	11	12	6-2267061-2
OBSOLETE	△ ₄	27.53 [1.084]	25.40 [1.000]	10	11	6-2267061-1
OBSOLETE	△ ₄	24.99 [.984]	22.86 [.900]	9	10	6-2267061-0
OBSOLETE	△ ₄	22.45 [.884]	20.32 [.800]	8	9	5-2267061-9
OBSOLETE	△ ₄	19.91 [.784]	17.78 [.700]	7	8	5-2267061-8
OBSOLETE	△ ₄	17.37 [.684]	15.24 [.600]	6	7	5-2267061-7
OBSOLETE	△ ₄	14.83 [.584]	12.70 [.500]	5	6	5-2267061-6
OBSOLETE	△ ₄	12.29 [.484]	10.16 [.400]	4	5	5-2267061-5
OBSOLETE	△ ₄	9.75 [.384]	7.62 [.300]	3	4	5-2267061-4
OBSOLETE	△ ₄	7.21 [.284]	5.08 [.200]	2	3	5-2267061-3
OBSOLETE	△ ₄	4.67 [.184]	2.54 [.100]	1	2	5-2267061-2
OBSOLETE	△ ₄	2.13 [.084]	-	-	1	5-2267061-1

FINISH	C	B	A	NO OF POSN	PART NUMBER
--------	---	---	---	------------	-------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03FEB2014 NAGALAKSHMI K	 TE Connectivity Ltd.
DIMENSIONS: mm [INCHES]		CHK 03FEB2014 MILLER MICHAEL	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ANGLES ± -		APVD 03FEB2014 MILLER MICHAEL	NAME ASSEMBLY, MOD II, HEADER, SINGLE ROW, 2.54[.100]C/L VERTICAL, 0.64[.025] SQ POSTS
MATERIAL FINISH		PRODUCT SPEC APPLICATION SPEC	SIZE A2
		WEIGHT -	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO C-2267061
		SCALE 4:1	RESTRICTED TO -
		SHEET 2 of 2	REV A1