

4

3

2

1





THIS DRAWING IS UNPUBLISHED.      RELEASED FOR PUBLICATION      -.-  
 © COPYRIGHT - by -      ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD		
-	-	-	-	-	-	-	-

- PRODUCT SPECIFICATION:
1. Rated Current: 2.0AMP.
  2. Contact Resistance: 20mΩ Max.
  3. Withstand Voltage: 1000V AC/DC
  4. Insulation Resistance: 1000MΩ Min.
  5. Operation Temperature: -40°C to +105°C
  6. Recommend Soldering Process:  
Wave Soldering 260°
  7. Packaging: Tube

MATERIAL:  
 CONTACT: COPPER ALLOY  
 HOUSING: HIGH-TEMPRETURE PLASTIC,  
 UL94V-0 BLACK

FINISH:  
 GOLD FLASH ALL OVER NICKEL



Recommended P.C.B Layout

PART NUMBER AS SHOWN: 2271010-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ETHAN CHENG 25-NOV-13	TE Connectivity	
		CHK KOBBY ZHAO 26-NOV-13		
DIMENSIONS: mm		APVD XU XIANG 27-NOV-13	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	AMPMODU, 2.00PITCH, 24 POSITION, PIN HEADER, RA, THROUGH HOLE	
0 PLC ± -		108-137777	RESTRICTED TO	
1 PLC ± -		APPLICATION SPEC	-	
2 PLC ± 0.25		WEIGHT	SIZE	CAGE CODE
3 PLC ± -		-	A2	00779
4 PLC ± -		CUSTOMER DRAWING	DRAWING NO	SCALE
ANGLES ± -		-	2271010	1:1
FINISH		-	SHEET	1 of 1
SEE NOTES		-	REV	A

4

3

2

1