

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19




© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LDC DS DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	□	RELEASED	'95 12/19	JW	BM
	A	REVISED ECN(RD97-098)	'97 5/22	YJ	JK
	B	REVISED ECN(RD97-240)	'97 NOV/12	JW	CS



NOTES

- ① 1. MATING UPPER HSG P/N : 85124-1(NATURAL)
MATING LOWER HSG P/N : 368004-1(BLACK)
- 2. APPLICABLE REC. CONTACT P/N

PART NO	DESCRIPTION	WIRE SIZE(mm ²)	CURRENT(A)
170209	Jr Timer REC	0.5 - 2.0	MAX. 20
170439	↑	0.3 - 0.5	MAX. 5

- 3. APPLICABLE PLUG ASS'Y P/N : 85251
- △ AMP TRADE MARK & LOGO.
- △ CABITY MARK

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN	AMP AMP KOREA. kyungsan, korea		
DIMENSIONS: MM		CHK			
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 <XX<10 ± 0.2 10<XX<30 ± 0.25 30<XX ± 0.3 ANGLES ± 3°		APVD	NAME PLUG HSG ASS'Y FOR J-TIMER 55P COVER ASS'Y(RHD TYPE)		
3rd ANGLE PROJECTION		PRODUCT SPEC	DRAWING NO		
MATERIAL NYLON66 GF15		APPLICATION SPEC	SIZE A3	CAGE CODE 00779	DRAWING NO C- 368005
FINISH		WEIGHT	SCALE 1/1	SHEET 1 OF 1	REV B