

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC GP DIST 00

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	25MAY2015	TB	AVZ

NOTES:

- 1 EACH ITEM AND ASSEMBLY MUST COMPLY WITH EUROPEAN REDUCTION OF HAZARDOUS SUBSTANCES (RoHS) REGULATION. UNDER DIRECTIVE 2011/65/EU AND HARMONIZED STANDARD EN 50581:2012.
- 2 DO NOT SOLDER CONTACT, CRIMP ONLY
- 3 IDENTIFY POSITION PE, LOADING POSITIONER PE TO SOCKET PE
- 4 PE CONTACT CIRCUIT IDENTIFIED BY EXTENDED LENGTH POLARIZED "KEY"
- 5 ELECTRICAL TEST:
100% OPEN SHORT&MISS WIRE TEST
CONTACT RESISTANCE: 2 OHM MAX

TE PN
2829488-1

1219.2±25.4





CONNECTOR 1

CONNECTOR 2

WIRE DIAGRAM

CONNECTOR 1	WIRE COLOR	CONNECTOR 2
L1	BROWN	L1
N	BLUE	N
L3		L3
S2	GRAY	S2
S1	BLACK	S1
L2		L2
PE	GREEN/YELLOW	PE

5	PC	14 AWG Socket Contacts	8
1	PC	Socket Housing Assembly 5 POS. A CODING	7
AR	M	Cable, H07RN-F, 14/5 Black, 13.3-17.0mm OD (Mueller 4101405)	6
2	PC	Cable Ring Nut 14-17mm OD	5
2	PC	Cable Clamp/Seal Assembly 14-17mm OD	4
2	PC	Contact/Positioner Assembly	3
5	PC	14 AWG Pin Contacts	2
1	PC	Pin Housing Assembly 5 POS. A CODING	1
-1	UoM	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.BURZYŃSKI 25MAY2015	 TE Connectivity	
DIMENSIONS: mm		CHK A.V.ZANDVOORT 25MAY2015		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A.V.ZANDVOORT 25MAY2015	NAME SEALED 567 POS PIN TO SEALED 567 POS SOCKET STD HARMONIZED CABLE	
 0 PLC ± 0,5 1 PLC ± 0,5 2 PLC ± 0,5 3 PLC ± - 4 PLC ± - ANGLES ± 2		PRODUCT SPEC -	SIZE A3	
MATERIAL -		FINISH -	APPLICATION SPEC -	CAGE CODE 00779
		WEIGHT -	DRAWING NO C-2829488	RESTRICTED TO -
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1
			REV A	