

RECOMMENDED MOUNTING HOLES AND CLEARANCE AREA
TOLERANCE UNLESS OTHERWISE SPECIFIED, ±.006

SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

- UL RECOGNIZED: UL 1283
- CSA CERTIFIED: CSA 22.2, NO.0,0.4, 8
- VDE APPROVED: EN 133 200

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 3 AMP, 120/250 VAC,
3 AMP/40°C, 250 VAC

LINE FREQUENCY: 50-60Hz

MAXIMUM LEAKAGE CURRENT,
EACH LINE TO GROUND: 0.3mA @ 120V 60Hz
0.5mA @ 250V 50Hz

OPERATING AMBIENT TEMP. RANGE: -10°C TO +60°C @ RATED CURRENT, I_r .

IN AN AMBIENT, T_a , HIGHER THAN 60°C, THE MAXIMUM OPERATING CURRENT, I_o , IS AS FOLLOWS:

$$I_o = I_r \sqrt{\frac{85 - T_a}{25}}$$

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C
HUMIDITY: 21 DAYS @ 40°C 95% RH.
CURRENT OVERLOAD TEST: 6 TIMES RATED CURRENT FOR 8 SECONDS

TEST SPECIFICATIONS:


INDUCTANCE: 13.77 mH NOMINAL
CAPACITANCE: (MEASURED @ 1KHz, 0.25VAC MAX., 25°C±1°C)
LINE TO GROUND: 8000pF ±20%
LINE TO LINE: .74pF ±20%
DISCHARGE RESISTOR: 330 K Ω
LINE/GROUND AND LINE/LINE 6000M Ω (MIN.) @ 100VDC
INSULATION RESISTANCE 20°C AND 50% RH (WITHOUT DISCHARGE RESISTOR)

RECOMMENDED RECEIVING INSPECTION HIPOT:


LINE TO GROUND: 2250VDC FOR 1 MINUTE
LINE TO LINE: 1450VDC FOR 1 MINUTE

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



50 Ω - 50 Ω (MINIMUM) INSERTION LOSS										
FREQUENCY MHz	.01	.03	.05	.07	.15	.50	1	5	10	30
COMMON dB	15	24	29	32	39	43	42	40	40	40
DIFF. dB	-	10	26	34	53	75	75	70	60	55



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION. HARRISBURG, PENNSYLVANIA USA

TOLERANCE EXCEPT AS NOTED
DECIMAL: .XXX .XX .X ANGLES ±1°
INCHES: ±.025
METRIC: ±
DIMENSIONS ARE IN INCHES UNLESS SPECIFIED

MATERIAL: AS SUPPLIED

FINISH:

CORCOM PRODUCTS, 620 S. BUTTERFIELD RD. MUNDELEIN IL 60060

POWER LINE FILTER

TYCO ELECTRONICS PART NO. 0-1609062-3

SCALE: NTS	DATE: 08AUG86	DRG. NO.	REV.
DRW. BY: LJD	ORIG: CFW	3E2P	4