


REV. 0
DCO 64253

TOL. = ±.010

COIL: @ 25°C	
SET	RESET
300 OHMS ±10%	300 OHMS ±10%
12 VDC NOMINAL VOLTAGE	12 VDC NOMINAL VOLTAGE
5.8 VDC MUST OPERATE	5.8 VDC MUST OPERATE
ENVIRONMENT:	
VIBRATION 10 Hz	3000 Hz 30 g's
SHOCK 100 g's	6 MS. DURATION
TEMPERATURE -65 °C	TO +125 °C
NOTES: SET AND RESET TIME 5 MS MAX.	
CONTACT BOUNCE 1.5 MS MAX.	



CONTACT RATING: LOW LEVEL TO 2A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. ASB 7 AUG 02 CK. *[Signature]*

CII Technologies
advanced control electronic solutions

CUST. QPL
CUST. NO. M39016/32-009
TYPE "3SAM" RELAY

3SAM1827A2