


P	LTR	DESCRIPTION	DATE	DWN	APVD
	C3	NOTE 1 PLATING INFO CORRECTED	03JUL2018	RK	PS
	C4	OBSOLETING THE PN 4-1437644-5, 4-1437644-9	28NOV2023	SP	PS

NOTES:

- 1 .032 THK BRASS, PLATED .0002 MIN HOT TIN DIPPED.
- 2 .032 THK BRASS, PLATED .0002 MIN BRIGHT TIN.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



5-1437644-1 AS SHOWN

3	7.425	2	J6-20	2-1447477-0
	5.925	2	J6-16	1-1447477-6
	4.800	2	J6-13	1-1447477-3
	4.050	2	J6-11	1-1447477-1
	3.675	2	J6-10	1-1447477-0
	2.925	2	J6-8	1447477-8
	2.550	2	J6-7	1447477-7
	2.175	2	J6-6	1447477-6
	1.425	2	J6-4	1447477-4
	1.050	2	J6-3	1447477-3
3	0.675	2	J6-2	1447477-2
	7.425	1	J6-20	4-1437644-8
	5.925	1	J6-16	4-1437644-6
	4.800	1	J6-13	4-1437644-5
	4.050	1	J6-11	4-1437644-4
3	3.675	1	J6-10	4-1437644-3
	2.925	1	J6-8	5-1437644-3
	2.550	1	J6-7	5-1437644-2
3	2.175	1	J6-6	5-1437644-1
	1.425	1	J6-4	5-1437644-0
	1.050	1	J6-3	4-1437644-9
	0.675	1	J6-2	4-1437644-7
	DIM A	MATERIAL	CATALOG NO.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S SCHLEGEL	8/4/04	STE TE Connectivity											
DIMENSIONS: in		CHK	S YODER	8/4/04												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	S YODER	8/4/04												
<table border="0"> <tr> <td>0 PLC</td> <td>±-</td> </tr> <tr> <td>1 PLC</td> <td>±-</td> </tr> <tr> <td>2 PLC</td> <td>±.02</td> </tr> <tr> <td>3 PLC</td> <td>±.010</td> </tr> <tr> <td>4 PLC</td> <td>±-</td> </tr> <tr> <td>ANGLES</td> <td>±1°</td> </tr> </table>		0 PLC	±-	1 PLC		±-	2 PLC	±.02	3 PLC	±.010	4 PLC	±-	ANGLES	±1°	NAME	
0 PLC	±-															
1 PLC	±-															
2 PLC	±.02															
3 PLC	±.010															
4 PLC	±-															
ANGLES	±1°															
MATERIAL		PRODUCT SPEC		-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO								
FINISH		APPLICATION SPEC		-	A3	00779	4-1437644-3	-								
		WEIGHT		-	CUSTOMER DRAWING		SCALE	SHEET								
							2:1	1 OF 1								
								REV C4								