



7 $5.08^{+0.05}_{-0.10}$ TYP
 1.00 ± 0.02 TYP
 $2.54^{+0.05}_{-0.10}$ TYP





264065-3 AS SHOWN

- 1 MATERIALS AND FINISH:
 HOUSING: HIGH TEMPERATURE POLYAMIDE, UL 94-V0, COLOR GREEN.
 TERMINAL: COPPER ALLOY, TIN PLATED.
2. SUITABLE FOR 1.6-2.4mm PC BOARD THK.
3. ELECTRICAL
 RATED VOLTAGE : 300 V
 RATED CURRENT : 12 A
 CONTACT RESISTANCE : < 15 mΩ
 INSULATION RESISTANCE: > 1000 MΩ (500V DC)
4. OPERATING TEMPERATURE RANGE: -40°C TO +110°C
5. P/N FROM 284065-4 TO 2-284065-5 ARE OBTAINED BY ASSEMBLING DIFFERENT MONOLITHIC MODULES CHOSEN AMONG: 284065-2 AND 284065-3, IN ORDER TO REALIZE THE DESIRED NO. OF WAYS.


6 MODULES AND KEYS TE BE GLUED IN PLACE.

7 NON CUMULATIVE TOLERANCE

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D		DESIGN IMPROVEMENT IN NEW MOLD	13AUG2020	DV	PS
E		REVISED AS PER PCN: E-20-012263	12OCT2021	SCB	SS
E1		DIM "A" TOL AND CURVATURE MAX DIM ADDED.	30DEC2021	SS	PS



RECOMMENDED PC BOARD LAYOUT



6													
6	0.6	±0.40	108.44	110.94	21	3-284065-3							
6	0.4	±0.25	77.96	80.46	15	3-284065-2							
6	0.6	±0.40	83.08	85.58	16	3-284065-1							
6			±0.50	123.68	126.18	24	3-284065-0						
6		±0.40	123.68	126.18	24	2-284065-9							
6			93.20	95.70	18	2-284065-8							
6	0.4	±0.25	83.08	85.58	16	2-284065-7							
6			62.72	65.22	12	2-284065-6							
6	0.6	±0.50	128.80	131.30	25	2-284065-5							
6			±0.40	123.68	126.18	24	2-284065-4						
6				118.64	121.14	23	2-284065-3						
6				113.56	116.06	22	2-284065-2						
6				108.44	110.94	21	2-284065-1						
6				103.40	105.90	20	2-284065-0						
6		0.4		±0.25	98.32	100.82	19	1-284065-9					
6			93.20		95.70	18	1-284065-8						
6			88.16		90.66	17	1-284065-7						
6			83.08		85.58	16	1-284065-6						
6			77.96		80.46	15	1-284065-5						
6			72.92		75.42	14	1-284065-4						
6	0.3	±0.20	67.84	70.34	13	1-284065-3							
6			62.72	65.22	12	1-284065-2							
6			57.68	60.18	11	1-284065-1							
6			52.60	55.10	10	1-284065-0							
6	0.1	±0.15	47.48	49.98	9	284065-9							
6			42.44	44.94	8	284065-8							
6	0.3	±0.20	37.36	39.86	7	284065-7							
6			32.24	34.74	6	284065-6							
6			27.20	29.70	5	284065-5							
6			22.16	24.66	4	284065-4							
6	0.1	±0.15	17.00	19.50	3	284065-3							
6			12.00	14.50	2	284065-2							
			CURVATURE MAX DIM "C" (SHEET 2)	DIM "A" TOL	DIM "A"	DIM "B"	POS	PART NUMBER					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.3
2 PLC	±0.25
3 PLC	±
4 PLC	±
ANGLES	±2°
FINISH	

MATERIAL:

FINISH:

DWN: S SCHLEGEL 07MAR2008
 CHK: C RICHARD 03JUL2008
 APVD: C RICHARD 03JUL2008

TE Connectivity

NAME: TERMINAL BLOCK, MULTIPLE HEADER. 180 DEGREE, CLOSED ENDS, 5.08mm PITCH


APPLICATION SPEC: 114-20079

SIZE: A2 CAGE CODE: 00779 DRAWING NO: C-284065


RESTRICTED TO: -

CUSTOMER DRAWING SCALE: 5:1 SHEET 1 OF 4 REV E1


P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-




2-284065-6




2-284065-9




2-284065-7




2-284065-8




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. SCHLEGEL 07MAR2008	 TE Connectivity
DIMENSIONS: mm		CHK C. RICHARD 03JUL2008	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. RICHARD 03JUL2008	NAME TERMINAL BLOCK, MULTIPLE HEADER. 180 DEGREE, CLOSED ENDS, 5.08mm PITCH
0 PLC ± 1 PLC ±0.3 2 PLC ±0.25 3 PLC ± 4 PLC ±		PRODUCT SPEC -	SIZE A2
ANGLES ±2° FINISH		APPLICATION SPEC 114-20079	CAGE CODE 00779
MATERIAL		WEIGHT -	DRAWING NO C-284065
		CUSTOMER DRAWING	RESTRICTED TO -
		SCALE 5:1	SHEET 2 OF 4
			REV E1


P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-




3-284065-0




3-284065-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 07MAR2008	 TE Connectivity	
DIMENSIONS: mm		CHK C RICHARD 03JUL2008		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C RICHARD 03JUL2008	NAME TERMINAL BLOCK, MULTIPLE HEADER. 180 DEGREE, CLOSED ENDS, 5.08mm PITCH	
0 PLC ±- 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±- 4 PLC ±- ANGLES ±2° FINISH		PRODUCT SPEC -	SIZE A2	CAGE CODE 00779
MATERIAL		APPLICATION SPEC 114-20079	DRAWING NO C-284065	RESTRICTED TO -
		WEIGHT -	SCALE 5:1	SHEET 3 OF 4
		CUSTOMER DRAWING	REV E1	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-		SEE SHEET 1	-	-	-



3-284065-2



3-284065-3

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 07MAR2008	 TE Connectivity	
DIMENSIONS: mm		CHK C RICHARD 03JUL2008		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C RICHARD 03JUL2008	NAME TERMINAL BLOCK, MULTIPLE HEADER. 180 DEGREE, CLOSED ENDS, 5.08mm PITCH	
0 PLC ±- 1 PLC ±0.3 2 PLC ±0.25 3 PLC ±- 4 PLC ±- ANGLES ±2° FINISH		PRODUCT SPEC -	SIZE A2	CAGE CODE 00779
MATERIAL		APPLICATION SPEC 114-20079	DRAWING NO C-284065	RESTRICTED TO -
		WEIGHT -	SCALE 5:1	SHEET 4 OF 4
		CUSTOMER DRAWING	REV E1	