

AMP * N SERIES PLUG CONNECTOR 228440-1



REDUCED FOR PACKAGING




Fig. 1

1. INTRODUCTION

This instruction sheet (IS) covers the use of the AMP N Series Plug Connector 228440-1 which is used with Type RG-402/U (.141) semi-rigid cable. The plug mates with N series jacks. Read these instructions thoroughly before using the plug.

2. DESCRIPTION (Figure 1)

The connector consists of the plug and adapter assembly 228446-1. The adapter assembly secures the plug to the cable.




Fig. 2

3. TOOL SELECTION

A. Hand Tool 59980-1

Refer to AMP Instruction Sheet IS 6788 for information concerning application of the adapter assembly with AMP Hand Crimping Tool 59980-1. Use AMP Crimping Dies 312253-1 and AMP Plug Locator 220220-2 with the hand crimping tool.

B. Pneumatic Tool 220239-1

Refer to AMP Instruction Sheet IS 2942 for information concerning application of the adapter assembly with AMP Pneumatic Tool 220239-1. Use AMP Crimping Dies 220243-1 and AMP Plug Locator 220241-1 with the pneumatic tool.

4. APPLICATION PROCEDURE

- 1. Prepare cable (see Figure 2) and determine the jack to be used with the plug.
- 2. Slide adapter assembly over cable and crimp with the selected crimping tool.
- 3. Thread adapter assembly and cable into plug, and tighten assembly with a torque wrench to a torque of 7 to 10 in.-lb.
- Thread plug into jack and tighten.