


LOC	DIST	REVISIONS			
		P	LTR	DATE	OWN
		L1	DRAWING MAINTENANCE	12-16-05	JDM/MKS

CODE
CDM 032-0025-0001

CABLE ACCEPTANCE DIMS.
JACKET D. ————.093 MAX.
DIELECTRIC D. ————.050 MAX.
CENTER CONDUCT. D. ————.013 MAX.



003-0270-0000	B.R. CAP	SILICONE RUBBER ZZ-R-165	7
003-0597-0001	SLEEVE	TEFLON PER L-P-403	6
005-2319-0001	RING	BRASS PER QQ-B-626	5
003-0326-0001	FERRULE	BRASS PER QQ-B-626	4
003-0029-0001	NUT	BRASS PER QQ-B-626	3
003-0027-0001	BUSHING	TEFLON PER L-P-403	2
003-0359-0002	PIN	BRASS PER QQ-B-626	1
COMPONENT NOMENCLATURE		MAT'L & SPEC	ITEM
NO			NO.

- 8 MALE DIAMOND KNURL
7 150-32 UNF-2B THREAD.
6 GOLD PLATE .00005 MIN. PER MIL-G-45204 TYPE II, CLASS I
5 SILVER PLATE .0002-.0004 PER QQ-S-365
4 DELETED
3. MALCO ASSY TOOL #T-3221 OR 010-0003-0000 REQD.
2. FOR ASSY INSTRUCTIONS SEE RF-ASMB-88.
1. THIS CONNECTOR MATES WITH ALL S-50 JACKS AND RECEPTACLES AS LISTED IN MALCO CATALOG
- NOTES: UNLESS OTHERWISE SPECIFIED

SEE TYCO TITLE BLOCK	
UPDATE REV LETTER	
ASSEMBLY	NO REQ'D
NEXT ASSEMBLIES	LET EGO
REVISION DESCRIPTION	

STANDARD TOLERANCES UNLESS OTHERWISE SPECIFIED DEC. IS .010 FRACTION 1/32 ANGLE 1/2 ECCENTRICITY MAX. TYP. HOLE DIA. ± .0015 SURFACE ROUGHNESS MICRO INCHES THREADS TO MIL-STD-208 COMMERCIAL TOLERANCES APPLY TO STOCK DIMENSIONS	MICRODOT INC. SOUTH PASADENA, CALIF.
SURFACE TREATMENT NOTED	MATERIAL NOTED
APPROVED BY G.R.F.	CHECKED BY M.F.M.
PROD CODE 931	SCALE 1/1
DATE 7-4-54	DRAWING NUMBER 032-0025-0001

PLUG

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN D. MORALES 12-16-05 CHK M. STORRY 12-16-05 APP M. STORRY 12-16-05	NAME M. STORRY
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1/32 1 PLC ± 2 PLC ± 3 PLC ± .010 4 PLC ± ANGLES ±	PRODUCT SPEC
MATERIAL		FINISH	APPLICATION SPEC
WEIGHT		—	RESTRICTED TO
CUSTOMER DRAWING		SCALE NONE	SHEET 1 of 1