




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	B	UPDATE PER ECO-14-019226		22 DEC 14	CAS	CAS	



- 1 SHELL MATERIAL: 6061-T6 ALUMINUM, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 OR SAE-AMS-2404
INSULATOR: DIALYL PHTHALATE, COLOR BLACK
INTERFACIAL SEAL: SILICONE RUBBER
- 2 INSTALL THREADED BUSHING INTO THE ASSEMBLY IN THE "A" POLARIZATION POSITION
- 3 CRIMP SOLDER POT ADAPTERS INTO THE SOCKET CONTACTS PER MEP 302-05
- 4 MARKING PER MEP 203-12, CODES C & E IN PRIMARY AREA, AND CODES B & D IN SECONDARY AREA, CODE J IN EITHER MARKING AREA (SIDE) THAT THE CODE WILL FIT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C SCHOLL	10 JUN 14		
DIMENSIONS: INCHES		CHK -	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C SCHOLL	10 JUN 14	NAME	
0 PLC ± -		PRODUCT SPEC		RECEPTACLE, METAL JACKMATE, 48 POSITION	
1 PLC ± -		APPLICATION SPEC		WITH SOLDER CUP TERMINATION	
2 PLC ± .01		WEIGHT		MCD P/N 095-9573-0024	
3 PLC ± .005		SCALE		RESTRICTED TO	
4 PLC ± -		6:1		-	
ANGLES ± 2°		SHEET		1 OF 1	
FINISH		REV		B	
SEE NOTES		CUSTOMER DRAWING		-	