

# Single Pole, Electrically Held, 10 Amps and Less



BLUE BEAD Q Â Ç

**Terminal View** 

## **Product Facts**

- Hermetically sealed
- Up to 10 amps switching
- High shock & vibration ratings
- Optional terminals & mounting styles

**Electrical Characteristics** Contact Arrangement — 1 Form C (SPDT) Contact Material -Stationary — Hardened silver alloy Moveable — Hardened silver alloy Contact Resistance -Before Life — 50 Milliohms max.

(measured at 10 mA @ 6 Vdc) After Life — 100 Milliohms max. (measured @ 1 A @28 Vdc)

Contact Rating -Contact Load — 10 A 28 Vdc Type — Resistive Operations min. 50,000

Mechanical Life Expectancy — 1 million operations min. Coil Voltage — 6 to 26.5 Vdc

Coil Power — 1.4 watts max. @ 25°C

Duty Cycle — Continuous Pick-up Voltage — Approximately 50% of nominal coil voltage Pick-up Sensitivity — 260 mW

# **Operational Characteristics**


Operate Time — 5.0 ms max. Release Time — 5.0 ms max. Contact Bounce — 5.0 ms max. Dielectric Withstanding Voltage —

Between Open Contacts -500 Vrms 60 Hz Between Adjacent Contacts ----1000 Vrms 60 Hz Between Contacts and Coils -----1000 Vrms 60 Hz

Insulation Resistance — 1,000 megohms min. @ 500 Vdc


#### **Environmental Characteristics** Temperature Range — -65°C to +125°C

Weight — 0.28 oz. (8 grams) max. Vibration Resistance -20 G's. 10 to 2.000 Hz Shock Resistance — 100 G's, 6 ±1 ms Designed To --- MIL-R-39016





.050 DIA 030 DIA (1.27) ¥. ntact 3 ninal Coil Te .160 ±.010 .252 ±.010 (6.4 ±.25) (4.1 + 25)BLUE BEAD -.200 (5.08) (5.08 .600 .600 (15.24)



Terminals

## **Standard Coil Data**

Nom. Coil Voltage (Vdc)	Coil Resistance in Ohms ±10% @ 25°C	Pickup Voltage Vdc (Max.) @ 25°C	Pickup Voltage Vdc (Max.) @ 125°C	Drop-out Voltage Vdc (Min.) @ 25°C	Drop-out Voltage Vdc (Min.) @ -65°C	Nom. Coil Power (W) @ 25°C	Max. Coil Voltage	Coil Desig.
6.0	40	3.5	4.5	0.45	0.3	.9	8.0	6
12.0	160	6.5	9.0	0.9	0.6	.9	15.0	12
26.5	700	14.0	18.0	1.8	1.2	1.0	32.0	24

Specifying a Part Number Exam

nple:	<u>Туре</u>	<u>Mountings</u>	<u>Contacts</u>	<u>Coils</u>	<u>Terminals</u>	
	С	BW-	1C-	24	B	
s are shown for urposes only. Ins subject	Dimensions are in millimeters unless otherwise specified.		USA: +1 800 522 6752 Asia Pacific: +86 0 400 UK: +44 800 267 666		For additional support numbers please visit www.te.com	

1 - 70

www.te.com

Revised 3-13

Catalog 5-1773450-5 reference pu Specification to change.

Dimensions