


P	LTR	DESCRIPTION	DATE	DWN	APVD
	G2	REVISED PER ECO-11-004820	11MAR11	RK	HMR
	G3	REVISED PER ECO-17-007400	29NOV2017	RS	DR



AMP WIRE RANGE	E13288 Listed	LR7189 Certified
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED

- 1 BODY MATERIAL THICKNESS = 0.787±0.051[.031±.002]
- 2 FOR $\phi 2.667[\phi .105]$ TO $\phi 3.556[\phi .140]$ WIRE INSULATION.
- 3 STAMP AMP 22-18* APPROX AS SHOWN.
22-16 TERMINALS ARE STAMPED
22-18 IN ACCORDANCE WITH
MILITARY SPEC SAE AS 7928.
COMMERCIAL RANGE IS 22-16.
- 4 APPLIES FROM EDGE OF METAL WIRE BARREL TO
CENTER OF STUD HOLE.
- 5 MATERIAL:
BODY & SLEEVE: COPPER (ASTM-B152)
INSULATION: NYLON.
- 6 FINISH:
BODY & SLEEVE: TIN PLATED (ASTM-B545)
INSULATION: COLOR-RED.

5000	ON TAPE	2-326861-1
1000	LOOSE PIECE	326861
QTY	PACKAGE TYPE	PART NO

CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING TEMPERATURE:
105°C [221°F]


VOLTAGE RATING:
300V MAX

CIRCULAR MIL AREA:
0.26-1.65mm² [509-3,260]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:




- 0 PLC ± -
- 1 PLC ± -
- 2 PLC ± -
- 3 PLC ± 0.127[.005]
- 4 PLC ± -
- ANGLES ± .5°
- FINISH

MATERIAL



DWN	JR RUTH	15JUL09
CHK	TOM MICHIELUTTI	15JUL09
APVD	TOM MICHIELUTTI	15JUL09
PRODUCT SPEC	UL 486 A-B	
APPLICATION SPEC	114-2157	
WEIGHT	-	



WIRE-TERMINAL
PIDG-SPADE WIRE SIZE: 22-16 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=326861	-

CUSTOMER DRAWING SCALE 5:1 SHEET 1 OF 1 REV G3