


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LR	DESCRIPTION	DATE	DWM	APVD
P		REVISED PER ECR-18-017384	07NOV2018	ED	RS

- 1. CENTER CONTACT: CRIMPING TOOL M22520/2-01; POSITIONER M22520/2-20; SELECTOR SETTING PER TABLE
- 2. FERRULE: CRIMPING TOOL M22520/5-01; DIE NUMBER OR HEX SIZE PER TABLE
- 3. PRODUCT IS DESIGNED TO MEET PRODUCT SPECIFICATION 108-1574.
- 4. BRIGHT NICKEL PLATE.
- 5. COUPLING NUT MUST WITHSTAND 60 LB RETENTION FORCE. ALSO 15 IN-LB TORQUE WHEN MATED.
- 6. USE SELECTOR SETTING #7 FOR RG-142, 142A, 142B AND SELECTOR SETTING #6 FOR RG-400
- 7. INSTRUCTION SHEET: 408-4032



OBSOLETE	CABLE SIZE	DIE # OR HEX SIZE	SELECTOR SETTING	SHELL		FERRULE QTY=1	CONTACT QTY=1	PLUG ASSY QTY=1	PART NUMBER
				FINISH	MATERIAL				
	RG-55, 55 A, 55 B, 223	DIE M22520/5-11 A OR .213X.400 HEX	#7	4	BRASS	9-446556-3	443246-2	447844-1	1-5447647-0
	RG-174, 188 A, 316	DIE M22520/5-35 B OR .128X.400 HEX	#4	4	BRASS	9-446556-1	447869-2	447844-4	5447647-3
	RG-142, 142 A, 142 B, RG-400	DIE M22520/5-11 A OR .213X.400 HEX	6	4	BRASS	9-446556-0	443246-2	447844-1	5447647-2
	RG-58, 58 A/U, 58 B/U, 58 C/U	DIE M22520/5-11 A OR .213X.400 HEX	#5	4	BRASS	9-446556-2	443246-2	447844-1	5447647-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWM L VARELA - DOCK5 31JAN2005	TE Connectivity	
DIMENSIONS: INCHES TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - FINISH: ± -		CHK J HAVENER 31JAN2005 NAME D. CAMELIO PRODUCT SPEC: 108-1574 APPLICATION SPEC:	APVD 31JAN2005 SIZE CAGE CODE DRAWING NO A2 00779 ©=5447647 RESTRICTED TO:	
MATERIAL: SEE TABLE		WEIGHT: 0.000000		CUSTOMER DRAWING
		SCALE: 1:1		SHEET: 1 of 1

5447647