

# OSM Straight Cable Plug Compression Crimp Attachment 1050799–1

Instruction Sheet 408–4663 (was A.P. 20–565) 14 FEB 00 Rev O EC 0990–0137–00

### CONNECTOR TYPE

OSM STRAIGHT CABLE PLUG COMPRESSION CRIMP ATTACHMENT

# CABLE TYPE

RG-402/U .141 SEMI-RIGID COAXIAL CABLE


### TOOLS REQUIRED:

CRIMP TOOL:2598-5200-54

OPTIONAL TOOLS

PRODUCTON TOOLING AVAILABLE

UPON REQUEST




DIM A .690 MAX .568 MAX

BEFORE CRIMP AFTER CRIMP

#### ASSEMBLY OPERATIONS


## 1.0 PREPARATION OF CABLE

1.1 TRIM CABLE TO DIMENSION SHOWN.




#### 2.0 SHAPE INNER CONDUCTOR OF CABLE

2.1 SHAPE BLUNT END OF INNER CONDUCTOR TO AN 85°-90° CONE.



## 3.0 INSTALL CABLE INTO CONNECTOR ASSEMBLY

- 3.1 INSTALL LOWER CABLE SUPPORT (FOR .141 CABLE) AND ANVIL (SMA/M) INTO CRIMP TOOL.
- 3.2 SET CRIMP LENGTH ON CRIMP TOOL TO .441
- 3.3 CAREFULLY INSERT CABLE INNER CONDUCTOR INTO PRE-ASSEMBLED CENTER CONTACT OF CONNECTOR ASSEMBLY UNTIL CABLE BOTTOMS ON SHOULDER IN CONNECTOR ASSEMBLY.
- 3.4 PLACE ASSEMBLY INTO CRIMP TOOL, BOTTOMING THE CONNECTOR REFERANCE PLANE AGAINST ANVIL AND ALLOWING THE CABLE TO SETTLE IN THE LOWER CABLE SUPPORT.
- 3.5 SQUEEZE HANDLES OF CRIMP TOOL UNTIL RATCHET RELEASES.
- 3.6 ASSEMBLY IS NOW COMPLETE.



#### ADHERENCE TO STEPS GIVEN WILL YIELD TOLERANCES SHOWN ON M39012/79

| MILITARY P/N   | M/A-COM P/N                  | DIM |
|----------------|------------------------------|-----|
| M39012/79B     | PASSIVATE                    | B   |
| 3004<br>3104 * | 2001-8204-92<br>2001-8304-92 |     |

\* NO SAFETY WIRE HOLES.