


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	17	A1	REVISED CAP	30MAY07	KH JD



- 1 DIMENSIONS IN [] ARE IN INCHES
- 2 MAXIMUM INSERTION LOSS IS 0.5dB PLUS CABLE ATTENUATION OF 0.7dB/km AT 1310nm. (SEE TABLE)
- 3 55 dB MIN RETURN LOSS (FC)
65 dB MIN RETURN LOSS (FC/APC)
4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702

0.64	200±2.0 [7874±79]	9-5492190-9
0.52	40.00±0.40 [1575.0±16.0]	4-5492190-0
0.52	35±0.35 [1378±14]	3-5492190-5
0.52	30±0.3 [1181±12]	3-5492190-0
0.52	25±0.3 [984±12]	2-5492190-5
0.51	20±0.30 [787±12]	2-5492190-0
0.51	15±0.15 [591±6]	1-5492190-5
0.51	12±0.15 [472±6]	1-5492190-2
0.51	10±0.15 [394±6]	1-5492190-0
0.50	7±0.08 [275±3]	5492190-7
0.50	6±0.08 [236±3]	5492190-6
0.50	5±0.08 [197±3]	5492190-5
0.50	3±0.05 [118±2]	5492190-3
0.50	2±0.05 [79±2]	5492190-2
0.50	1±0.05 [39±2]	5492190-1
MAX IL (dB)	L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	C.S.VASU	10 FEB 06	Tyco Electronics Corporation Harrisburg, Pa 17105-3608
DIMENSIONS: METERS [INCHES]		CHK	J.DUNCAN	10 FEB 06	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	J.DUNCAN	10 FEB 06	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	NAME		
MATERIAL		APPLICATION SPEC		CABLE ASSEMBLY, SINGLEMODE LDS, FC/APC TO FC/UPC	
FINISH		WEIGHT	SIZE		RESTRICTED TO
-		-	A2	CAGE CODE 00779	DRAWING NO. C=5492190
CUSTOMER DRAWING			SCALE	SHEET	REV
			NTS	1 OF 1	A1

5492190

A