

4



3

2



1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	REVISED AS PER ECN-24-251012	05FEB2024	JK	WH



- 1 MATERIAL: HOUSING – HTN NYLON, BLACK, UL 94V-0.  
TERMINALS – 0.33[.013] THICK PHOS BRONZE PLATED WITH 1.27 $\mu$ m[.000050] MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 3.81 $\mu$ m[.000150] MINIMUM THICK MATTE TIN IN SOLDER AREA OVER 1.27 $\mu$ m[.000050] MINIMUM THICK NICKEL UNDERPLATE.
- △ JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
- 3. DIMENSIONS ARE NOMINAL UNLESS OTHERWISE SPECIFIED.



SUGGESTED PANEL CUTOUT

SUGGESTED PC BOARD LAYOUT  
VIEW SHOWN IS TOP OF PC BOARD  
(COMPONENT SIDE)

5558065-1  
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. MAYBERRY/L.A.MAYER 01JUNE2005	TE Connectivity	
DIMENSIONS: mm		CHK J.WESTMAN 01JUNE2005	NAME S.FLICKINGER 01JUNE2005	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13[.005] 4 PLC ± - ± - ANGLES ± - ± -		PRODUCT SPEC		MODULAR JACK ASSEMBLY, 10 POSITION, SIDE ENTRY, LOW PROFILE
MATERIAL SEE NOTE 1		APPLICATION SPEC		RESTRICTED TO
FINISH SEE NOTE 1		WEIGHT 0.000000	SIZE A2	CAGE CODE 00779
		DRAWING NO C=5558065		SCALE 4:1
		CUSTOMER DRAWING		SHEET 1 of 1
				REV A2

5558065

A