

# SPECIFICATION CONTROL DRAWING

55A1121

Title TWO CONDUCTOR CABLE, SHIELDED, JACKETED, GENERAL PURPOSE, 600 VOLT

Date 28MAR11

Revision B1

This specification sheet forms a part of the latest issue of Raychem Specification 55A.



CABLE CONSTRUCTION DETAILS							
PART NUMBER 1/	CONDUCTOR SIZE (AWG)	SHIELD SIZE (AWG)	JACKET THICKNESS (in.)		OUTSIDE DIAMETER (in.)		MAXIMUM WEIGHT (lb/1000 ft)
			MINIMUM	NOMINAL	NOMINAL	MAXIMUM	
55A1121-30-*	30	38	.006	.008	.081	.086	5.4
55A1121-28-*	28	38	.006	.008	.087	.092	6.3
55A1121-26-*	26	38	.006	.008	.097	.102	7.9
55A1121-24-*	24	38	.006	.008	.107	.112	9.8
55A1121-22-*	22	38	.006	.008	.119	.125	12.2
55A1121-20-*	20	38	.006	.008	.135	.141	16.2
55A1121-18-*	18	38	.006	.008	.155	.162	21.9
55A1121-16-*	16	38	.006	.008	.171	.178	26.7
55A1121-14-*	14	38	.006	.008	.205	.213	38.4
55A1121-12-*	12	38	.007	.009	.243	.251	55.1
55A1121-10-*	10	38	.007	.009	.291	.306	83.1
55A1121- 8-*	8	36	.008	.010	.417	.438	152.

### CABLE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C  
 Maximum continuous conductor temperature  
 VOLTAGE RATING: 600 volts (rms) at sea level  
 ACCELERATED AGING: 300 ± 3°C for 7 hours  
 BLOCKING: 200 ± 3°C for 6 hours  
 DIELECTRIC WITHSTAND: 1500 volts (rms), 60 Hz  
 FLAMMABILITY: Procedure 1,  
 3 seconds (maximum); 3 inches (maximum);  
 no flaming of facial tissue  
 JACKET COLOR: White preferred  
 JACKET ELONGATION AND TENSILE STRENGTH:  
 Elongation, 50% (minimum)  
 Tensile Strength, 5000 lbf/in<sup>2</sup> (minimum)  
 JACKET FLAWS:  
 Spark Test, 1000 volts (rms)  
 Impulse Dielectric Test, 6.0 kV (peak)

LIFE CYCLE: 200 ± 3°C for 168 hours  
 LOW TEMPERATURE-COLD BEND: -65 ± 2°C for 4 hours  
 SHIELD COVERAGE: 85% (minimum)  
 VOLTAGE WITHSTAND TEST (Post Environmental):  
 1000 volts (rms), 60 Hz, 1 minute

PART NUMBER:  
 The "\*" in the part numbers above shall be replaced by color code designators with a slash separating the component wire colors and a dash separating the component wire colors from the jacket color.  
 1/ Example: AWG 22, blue and white component wires; white jacket: 55A1121-22-6/9-9

NOTE: Nominal values are for information only.  
 Nominal values are not requirements.

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.  
 TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. HOWEVER, DUE TO LENGTH LIMITATIONS OF THE RAYCHEM PART NUMBER, AN ALTERNATIVE COLOR CODE MAY REPLACE MIL-STD-681 COLOR CODE DESIGNATORS. (EXAMPLE: "901/902..." MAY BE REPLACED BY "Axxx") OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.