

SPECIFICATION CONTROL DRAWING

55PC0111

TITLE WIRE, RADIATION-CROSSLINKED, MODIFIED ETFE-INSULATED, LIGHTWEIGHT, GENERAL PURPOSE, 600 VOLT


Date
28-Mar-11

Revision
E1

This specification sheet forms a part of the latest issue of Raychem Specification 55PC.

CONDUCTOR - TIN-COATED COPPER

INSULATION - RADIATION - CROSSLINKED,
MODIFIED ETFE



CONSTRUCTION DETAILS

PART NUMBER 1/	WIRE SIZE (AWG)	CONDUCTOR STRANDING (number x AWG)	CONDUCTOR DIAMETER (in.)			MAXIMUM RESISTANCE AT 20°C (ohms/1000 ft.)	FINISHED WIRE DIAMETER (in.)			WEIGHT (lbs/1000 ft.)	
			LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT		LOWER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT	TARGET VALUE	UPPER SPEC LIMIT
55PC0111-30-*	30	7 x 38	.0110	.0115	.0120	108.4	.0221	.0235	.0249	.60	.64
55PC0111-28-*	28	7 x 36	.0140	.0145	.0150	68.6	.0251	.0265	.0279	.84	.89
55PC0111-26-*	26	19 x 38	.0175	.0183	.0191	41.3	.0291	.0305	.0319	1.23	1.34
55PC0111-24-*	24	19 x 36	.0225	.0233	.0241	26.2	.0341	.0355	.0369	1.81	1.93
55PC0111-22-*	22	19 x 34	.0285	.0293	.0301	16.2	.0401	.0415	.0429	2.69	2.83
55PC0111-20-*	20	19 x 32	.0365	.0375	.0385	9.88	.0481	.0495	.0509	4.11	4.27
55PC0111-18-*	18	19 x 30	.0452	.0464	.0476	6.23	.0573	.0590	.0607	6.27	6.56
55PC0111-16-*	16	19 x 29	.0514	.0527	.0538	4.81	.0646	.0665	.0684	8.01	8.33
55PC0111-14-*	14	19 x 27	.0644	.0659	.0674	3.06	.0789	.0810	.0831	12.39	12.81
55PC0111-12-*	12	37 x 28	.0825	.0845	.0865	2.02	.0974	.1000	.1026	19.17	19.71
55PC0111-10-*	10	37 x 26	.1050	.1070	.1090	1.26	.1220	.1260	.1300	30.68	31.70
55PC0111-8-*	8	133 x 29	.158	.163	.169	.701	.183	.188	.193	57.7	59.9

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice.
TE Connectivity also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

1/ COLORS AND COLOR CODE DESIGNATORS SHALL BE IN ACCORDANCE WITH MIL-STD-681. OTHER CODES AND SUFFIXES MAY BE ADDED TO THE PART NUMBER, AS NECESSARY, TO CAPTURE ANY ADDITIONAL REQUIREMENTS IMPOSED BY THE PURCHASE ORDER.

The TE logo, TE Connectivity and Raychem are trademarks.

DIMENSIONS ARE IN INCHES, AND UNLESS OTHERWISE DESIGNATED ARE NOMINAL.

THIS SPECIFICATION SHEET TAKES PRECEDENCE OVER DOCUMENTS REFERENCED HEREIN.
REFERENCED DOCUMENTS SHALL BE OF THE ISSUE IN EFFECT ON DATE OF INVITATION FOR BID.



TE Connectivity Wire & Cable
501 Oakside Avenue
Redwood City, CA 94063-3800
Phone: 1-800-227-8816
Fax: 1-650-361-6297

WIRE RATINGS AND ADDITIONAL REQUIREMENTS

TEMPERATURE RATING: 150°C

Maximum continuous conductor temperature

VOLTAGE RATING: 600 volts (rms) at sea level

COLOR: White preferred

CROSSLINK VERIFICATION: 300 ± 3°C for 1 hour

IDENTIFICATION AND COLOR STRIPING DURABILITY:

125 cycles (250 strokes) (minimum), 500 g weight

INSULATION ELONGATION AND TENSILE STRENGTH:

Elongation, 50% (minimum)

Tensile Strength, 5000 lbf/in² (minimum)

INSULATION FLAWS:

Spark Test, 3.0 kV (rms)

Impulse Dielectric Test, 8.0 kV (peak)

INSULATION THICKNESS: .006 in. (nominal)

SHRINKAGE: 230 ± 3°C for 1 hour, 0.125 inch (maximum) in 12 inches.

VOLTAGE WITHSTAND (Post Environmental): 2500 volts (rms)

PART NUMBER:

The “*” in the part numbers on page 1 shall be replaced by a color code designator.

1/ Example: AWG 22, white: 55PC0111-22-9

AWG 22, white with black stripe: 55PC0111-22-90

1/ See footer section on page 1