





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
H2		REVISED PER ECR-22-160893	15DEC2022	DB	BW



- 1 FASTON TERMINALS, BASE P/N 1742110, ARE USED IN THIS PRODUCT.
- △ 2 TIN PLATE PER MIL-T-10727.
- 3 MATING TAB THK TO BE 0.51±0.025 [.020±.001]
- 4 WIRE SIZE IS [#18-#16 OR TWO #18'S] AWG.
- 5 INSULATION RANGE IS 2.67-5.33 OR TWO AT 2.67 MAX, [.105-.210 OR TWO AT .105 MAX].
- △ 6 OBSOLETE PART

6/6 NYLON, VO - NAT(WHITE)	BRASS - TIN PL △ 2	521586-2
6/6 NYLON, VO - NAT(WHITE)	BRASS - PLAIN	<del>521586-1</del>
HOUSING MATERIAL & COLOR	TERMINAL MATERIAL & FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	17DEC02		ASSEMBLY, RECEPTACLE, ULTRA-POD, 4.8 [.187] SERIES		
DIMENSIONS: mm [INCHES]		CHK	N DEIBERT	17DEC02		NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	N DEIBERT	17DEC02		PRODUCT SPEC	108-1285	
0 PLC ± -		APPLICATION SPEC		114-2124		SIZE CAGE CODE DRAWING NO		
1 PLC ± -		WEIGHT		0.000000		A2 00779 C=521586		
2 PLC ± -		CUSTOMER DRAWING		SCALE		5:1 SHEET 1 OF 1 REV H2		
3 PLC ± 0.25 [.010]								
4 PLC ± -								
ANGLES ± -								
FINISH		SEE TABLE						