


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CE	16	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	ADD -11	24MAR09	LGE	JD

1. DIMENSIONS IN [ ] ARE IN INCHES
2. MAXIMUM CONNECTOR INSERTION LOSS IS 0.4dB PLUS CABLE ATTENUATION OF 0.7dB/km AT 1310nm. (SEE TABLE)
3. 50dB MINIMUM RETURN LOSS
4. TRACE LABEL PLACED ON ITS UNIT PACKAGE
5. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702



0.40	0.50±0.03 [19.7±0.98]	1-5492276-1
0.40	10.00±0.15 [393.70±5.91]	1-5492276-0
0.40	3.05±0.05 [120.0±2.0]	5492276-8
0.40	0.406±0.025 [16.00±0.98]	5492276-7
0.40	0.30±0.025 [11.81±0.98]	5492276-6
0.40	5.00±0.08 [196.85±3.15]	5492276-5
0.40	4.00±0.08 [157.48±3.15]	5492276-4
0.40	3.00±0.05 [118.11±1.97]	5492276-3
0.40	2.00±0.05 [78.74±1.97]	5492276-2
0.40	1.00±0.05 [39.37±1.97]	5492276-1
MAX IL (dB)	L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.S.VASU 22 MAR 06	Tyco Electronics Corporation Harrisburg, Pa 17105-3608													
DIMENSIONS: METERS [INCHES]		CHK J.DUNCAN 22 MAR 06	NAME CABLE ASSEMBLY, FIBER OPTIC, SINGLEMODE, BUFFERED FIBER, SC (NG) TO SC (NG), OPTIMATE													
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.DUNCAN 22 MAR 06	PRODUCT SPEC -													
<table border="0"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± -</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± -</td></tr> </table>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	APPLICATION SPEC -	SIZE A3	CAGE CODE 00779
0 PLC	± -															
1 PLC	± -															
2 PLC	± -															
3 PLC	± -															
4 PLC	± -															
ANGLES	± -															
MATERIAL -	FINISH -	WEIGHT -	DRAWING NO C-5492276	RESTRICTED TO -												
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1												
			REV A1													