



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	J1	REVISED PER ECN-24-273904	24JUL2024	SKN PS

1. THE CONTACT SURFACES OF THE TERMINALS ARE COATED WITH LUBRICANT.
2. ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY UNLESS OTHERWISE SPECIFIED.
3. MATERIAL:
 HOUSING - THERMOPLASTIC (BLACK)
 TERMINALS - HIGH STRENGTH COPPER ALLOY PLATED WITH EITHER .000030 MIN GOLD OR GOLD FLASH OVER PALLADIUM NICKEL .000030 MIN TOTAL, ON CONTACT MATING SURFACE. .000050 MIN NICKEL UNDERPLATE OVER ENTIRE TERMINAL.
4. WIRE SIZE: 22 AWG SOLID OR 22 AWG 7 STRANDS OF COPPER CONDUCTORS. MAX INSULATION DIAMETER OF .045 IS ACCEPTABLE FOR MOST APPLICATIONS.
5. CORING MAY OR MAY NOT APPEAR AND IS AT THE DISCRETION OF TYCO ELECTRONICS.

OBSOLETE

H:\Zach Ream\Millhimes\ECR-06-026488_ECO-06-026525\custc

OBSOLETE	AS SHOWN	552300-1
	DESCRIPTION	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. HOLT 12-17-79	 TE Connectivity	
DIMENSIONS: INCHES		CHK V.E. SLACK 12-17-79		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD B.G. WARD 12-17-79	NAME PLUG ASSY, 14 POSITIONS, C SLOT W/ 4-40 HOLES, CHAMP-LOK	
0 PLC ± -		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
1 PLC ± -		APPLICATION SPEC	A2 00779 C-552300	
2 PLC ± -		WEIGHT	CUSTOMER DRAWING	
3 PLC ± -		FINISH	SCALE NTS SHEET 1 OF 1 REV J1	
4 PLC ± -		ANGLES		

552300