



OBSOLETE



GUARD DETAIL
-2 ONLY

- 5 USE MANUAL PRECISION ADJUSTMENT LEVER ON G TERMINATOR TO ACHIEVE PROPER CRIMP HEIGHT.
- 6 ITEM NOT SHOWN
- 7 ITEM 81 IS ATTACHED TO THE G TERMINATOR GUARD DOOR WITH ITEM 80.
- 8 CRIMPER BOLT MUST BE LOOSEENED TO CHANGE CRIMP HEIGHT ADJUSTING WHEEL. BE SURE TO SEAT THE CRIMPER AGAINST THE ADJUSTING WHEEL AND REALIGN THE TOOLING.
- 9 CUT TO LENGTH AT ASSEMBLY.

LOC	A
DIST	66

		L1	REVISED PER ECR-23--187524						TE	
		L	ECR-15-018000						LG	
		K	ECR-15-009539						RS	
		J	ECR-14-012131						TE	
		H	ECR-11-025988						SX	
		G1	ECR-11-023910						SX	
P	F	LTR	REVISION RECORD						APP	

DIMENSIONS IN INCHES: DO NOT SCALE PRINT.		MATL		HT TR		FIN	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		DR 11/3/99		APP 11/3/99		TE Connectivity Harrisburg, PA 17105-3608	
2 PLG DEC ±.25		K.STAKEM		T.ELBIN			
2 PLG DEC ±		CHK 11/3/99		REL			
7 PLG DEC ±		C.ERISMAN		T			
8 PLG DEC ±							
2 ANGLES ±		NAME		END FEED		MACHINE REF	
SURF TEXTURE: √				PIGTAIL		G-SPICE	
1 REMOVE BURRS, BREAK		SCALE		DWG NO		SHEET	
1 DATE		- D		566393		1 of 1	
SHARP EDGES R.015 MAX						REV	
						U	