# SPECIFICATION CONTROL DRAWING




77 OHM, AWG 24, 19 STRANDS OF AWG 36, OPTIMIZED DOUBLE SHIELDS, DATA BUS CABLE, MIL-STD-1553 Date: 9-21-22 Revision: F

7724C3864

THIS SPECIFICATION SHEET FORMS A PART OF THE LATEST ISSUE OF RAYCHEM SPECIFICATION 1200.

## **CONSTRUCTION DETAILS**

DIMENSIONS ARE NOMINAL VALUES IN INCHES, UNLESS OTHERWISE



.113

.130

.190

#### CONDUCTORS

AWG 24, 19 Strands of AWG 36, Silver-Coated High-Strength Copper Alloy

#### **DIELECTRICS**

Radiation-Crosslinked, Modified ETFE Colors - Light Blue/White

### **FILLERS**

Radiation-Crosslinked, Modified ETFE



AWG 38, Tin-Coated Copper, Optimized

#### 2nd SHIELD

AWG 38, Tin-Coated Copper, Optimized

JACKET Zerohal

# **ELECTRICAL CHARACTERISTICS**

CHARACTERISTIC IMPEDANCE 77 ± 5 ohms, Method C at 1 MHz

MUTUAL CAPACITANCE 30.0 pF/ft. (maximum)

ATTENUATION 1.4 dB/100 ft. (maximum) at 1 MHz

SURFACE TRANSFER IMPEDANCE 10 milliohms/meter (maximum)

at 30 MHz

## ADDITIONAL REQUIREMENTS

# COMPONENT WIRE PRIOR TO CABLING (Test procedures per SAE AS22759)

CONDUCTOR RESISTANCE 26.5 ohms/1000 ft. (nominal)

CROSSLINKING PROOF TEST 300 ± 3°C for 1 hour, .625 inch mandrel,

.375 lb, 2.5 kV dielectric test

INSULATION (DIELECTRIC)

ELONGATION 50% (minimum)
TENSILE STRENGTH 5000 lbf/in² (minimum)

INSULATION FLAWS

SPARK TEST 3.0 kV (rms)
IMPULSE TEST 8.0 kV (peak)

INSULATION RESISTANCE 5000 megohms for 1000 ft. (minimum)

LOW TEMPERATURE-COLD BEND -65 ± 3°C for 4 hours. .750 inch mandrel.

1.00 lb, 2.5 kV dielectric test

SHRINKAGE 200 ± 3°C for 1 hour,

.125 inch (maximum) in 12 inches

# FINISHED CABLE

CABLE LAY LENGTH .75 inch (minimum), 1.25 inches (maximum)
FLAMMABILITY Method B, except 45 seconds (maximum)

HEAT SHOCK 225°C

JACKET

ELONGATION 150% (minimum)
TENSILE STRENGTH 1200 lbf/in² (minimum)

JACKET FLAWS

SPARK TEST 1.0 kV (rms)
IMPULSE TEST 6.0 kV (peak)

JACKET THICKNESS .030 inch (nominal)

LOW TEMPERATURE-COLD BEND -30°C/5.00 inch mandrel

VOLTAGE WITHSTAND

(DIELECTRIC)

VOLTAGE WITHSTAND

(Post Environmental)

1000 volts (rms), 1 minute

1500 volts (rms)

Designate outer jacket color with a dash number in accordance with MIL-STD-681. Unless otherwise specified, outer jacket color will be black (designated by a "-0" appended to the part number, e.g. 7724C3864-0).

Other codes and suffixes may be added to the part number, as necessary, to capture any additional requirements imposed by the purchase order.

WEIGHT 29.6 lbs/1000 ft. (nominal)

ENGINEERING REFERENCE

TEMPERATURE RATING 105°C (maximum)

Users should evaluate the suitability of this product for their application. Specifications are subject to change without notice. Tyco Electronics Corporation also reserves the right to make changes in materials or processing, which do not affect compliance with any specification, without notification to Buyer.

Page 1 of 1

Zerohal, Cheminax, Raychem, TE Connectivity, TE connectivity (logo), and TE (logo) are trademarks.

