



LOC	DIST	REVISIONS					
—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
VERWENDET FÜR 84-9714		2		CAD-NEUERSTELLUNG	14.05.90	A.HO	—
		3		REVISED PER ECO-09-023313	10OCT09	AEG	—
		4		ECR-10-025774	20JAN11	KK	HMR

ZEICHNUNG GÜLTIG AB 20/90

POLZ.	L±0.5	BESTELL-NR.
1	3.3	826 541-1
2	7.3	-2
3	11.3	-3
4	15.2	-4
5	19.2	-5
6	23.1	-6
7	27.1	-7
8	31.1	-8
9	35.1	-9
10	39.0	-0
11	43.0	-1
12	46.9	-2
13	50.9	-3
14	54.8	-4
15	58.8	-5
16	62.8	-6
17	66.7	-7
18	70.7	-8
19	74.7	-9
20	78.6	-0
21	82.6	-1
22	86.5	-2
23	90.5	-3
24	94.4	-4
25	98.4	-5
26	102.4	-6
27	106.3	-7
28	110.3	-8
29	114.2	-9
30	118.2	-0
31	122.2	-1
32	126.1	-2
33	130.1	-3
34	134.0	-4
35	138.0	-5
36	141.6	3-826 541-6



- 1 STECKSEITE: IM BEREICH "F" 0.8 μm GOLD ÜBER 1.27 μm NICKEL IM BEREICH "B"
- 2 LÖTSEITE: MIN. 2.5 μm ZINN ÜBER 1.27 μm NICKEL
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 3 OBSOLETE

KONTAKTSTIFT	Cu Zn	1
STIFTGEHÄUSE	PBTP GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. BY - COPYRIGHT -

DIMENSIONS: mm	DWN S.RIEGER 11.12.84	MATERIAL -	FINISH -
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3mm	CHK SCHAARSCHMIDT 11.12.84	TE Connectivity	
0 PLC ± -	APVD -		
1 PLC ± -	PRODUCT SPEC -	NAME AMPMODU I STIFTL. RASTER 3.96 EINREIHIG	
2 PLC ± -	APPLICATION SPEC -	SIZE A4	CAGE CODE 00779
3 PLC ± -	WEIGHT -	DRAWING NO C-826541	
4 PLC ± -		RESTRICTED TO -	
ANGLES ± -		SCALE 4:1	SHEET 1 OF 1
	CUSTOMER DRAWING	REV 4	