


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50	N2	REVISED PER ECR-19-013909	03OCT2019	PC MB



- CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 8.38 [.330] CENTERS.
- △ SLOT TERMINATES EITHER SINGLE OR DOUBLE MAGNET WIRES OF THE SAME TYPE AND SIZE, COPPER RANGE IS 0.36-0.57mm [#27-#23] AWG. ALUMINIUM RANGE IS 0.51-0.64mm [#24-#22] AWG, ALUMINIUM WIRE RANGE APPLIES FOR POST TIN PLATED PART NUMBERS ONLY.
- AFTER INSERTION INTO PLASTIC HOLDER TAB PORTION MUST BE BENT OVER 45° TO 90° OR POTTED-IN TO PREVENT PULL-OUT WHEN MATING RECEPTACLE IS DISCONNECTED.



BOX DOWN TAB BACK	62652-2
BOX DOWN TAB FOWARD	62652-1
REELING, LEFT TO RIGHT	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 1/3/91 MICHAEL S. FEHER	<b>STE</b> TE Connectivity		
DIMENSIONS: INCHES		CHK 1/14/91 JEFF R. RUTH			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 1/14/91 NELSON E. NEFF	NAME TAB, 6.35 [.250] FASTON™ MAG-MATE™		
0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC APPLICATION SPEC 114-2046	SIZE A2	CAGE CODE 00779	DRAWING NO C-62652
MATERIAL BRASS	FINISH TIN PLATE	WEIGHT -	SCALE 5:1	SHEET 1 of 1	REV N2
CUSTOMER DRAWING			RESTRICTED TO -		