

**AP-2000 Special Sizes
Modified Polyolefin, Adhesive Lined
Heat - Shrinkable Tubing**




Table 1: Dimensions



Size	Inside Diameter				Recovered Wall Thickness, Nominal (W)	
	As Supplied Minimum (D)		Recovered Maximum (d)			
	in	mm	in	mm	in	mm
No. 103	.788	20.0	.354	9.0	.039	1.0
No. 104	.906	23.0	.591	15.0	.039	1.0
No. 105	1.024	26.0	.709	18.0	.039	1.0
No. 106	1.182	30.0	.591	15.0	.039	1.0
No. 107	.748	19.0	.291	7.4	.056	1.4
No. 108	1.024	26.0	.354	9.0	.039	1.0

The tubing shall meet the requirements of TE specification RW-1001

Material

The outer jacket shall be fabricated from modified polyolefin and shall be crosslinked. The inner jacket shall be a meltable adhesive.

The dual wall tubing shall be homogeneous, free from flaws, defects, bubbles, pinholes, seams, cracks or inclusions and each wall shall be uniform.

AP-2000 SPECIFICATION CONTROL DRAWING				-----		-----	
						©2020 TE Connectivity Ltd. family of companies All Rights Reserved	
				DIMENSIONS IN inch (mm)	TITLE		
					AP-2000 Special Sizes Modified Polyolefin, Adhesive Lined Heat Shrinkable Tubing		
D1	ECR-21-105143	HD	25/06/2021	SHEET	NO	REV	
REV	ENGINEERING CHANGE	CHK	DATE	1 of 1	AP-2000 Tubing (Special Sizes)		D1