

WRAPTER FULL TENSION DEAD-ENDS GALVANISED STEEL

KEY FEATURES

- Uniform grip to stop any distortion of the conductor or damage to the conductor
- Type Tested to AS 1154 at an Independent NATA certified Mechanical laboratory
- Colour coding to the requirements of AS 1154.3
- Easy Installation by hand or live line methods, no need for any special tools

TE Connectivity are a leader in the design and supply of Helical Fittings for use on Utility and Distribution Networks across the ANZ region.

TE Connectivity can provide a wide range of WrapTEr helical terminations, joints, protection, restoration, repair and support fittings for use on bare and insulated overhead conductor. Each fitting is custom designed for a particular conductor range and type.

All fittings are manufactured from premium materials, which are compatible with the materials used in the conductor / cable onto which they are applied. This ensures maximum electrical and mechanical performance, whilst minimising corrosion potential.

FGD Full tension dead-ends are designed specifically to be used as a termination on SC/GZ style conductors.


Dead-ends are typically used for the termination of guy wires, stay conductors and earth wires.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.





On all SC/GZ style conductors, FGD fittings hold a minimum of 90% of the ultimate tensile strength of the conductor, onto which they are applied.



GALVANISED STEEL FULL TENSION DEAD-ENDS ORDERING INFORMATION					
TE Part Number	No. of Rods	Conductor Stranding	Conductor OD Range	Pack Quantity	Colour Code
FGD0370-0385-3	4	7/1.25	3.70 - 3.85	50	Green
FGD0420-0440-4	4	3/2.00	4.20 - 4.40	50	Yellow
FGD0465-0500-4	4	7/1.60	4.65 - 5.00	50	Black
FGD0550-0595-4	4	3/2.75	5.50 - 5.95	50	White
FGD0550-0595-4L*	4	3/2.75	5.50 - 5.95	50	White
FGD0595-0620-5	5	7/2.00	5.95 - 6.20	50	Yellow
FGD0790-0830-7	5	7/2.75	7.90 - 8.30	20	White
FGD0970-1020-7	5	7/3.25	9.70 - 10.20	20	Yellow/Orange
FGD1085-1170-7	6	7/3.75	10.85 - 11.70	20	Black
FGD1185-1220-7	6	7/4.00	11.85 - 12.20	15	Black
FGD1305-1395-8	5	19/2.75	13.05 - 13.95	5	White
FGD1600-1640-8	6	19/3.25	16.00 - 16.40	5	Orange

*Left hand lay

Unless specified otherwise, WrapTEr fittings are of right-hand lay. Please specify on the order if items are required for left-hand lay.

te.com/energy

©2015 TE Connectivity Ltd. family of companies. All Rights Reserved. AUDS-102-7/15

Raychem, TE Connectivity and TE Connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure. TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

FOR MORE INFORMATION: TE Customer Support Centers

NSW/QLD/NT/ACT:	+61 (2) 9554 2695
VIC/TAS/SA:	+61 (3) 9271 5243
WA:	+61 (8) 9358 7806
New Zealand:	+64 (9) 634 4580