


DRAWING NO: FAD1015-1050-6-C  
THIS DRAWING IS A CONTROLLED DOCUMENT



# CATALOGUE NUMBER: FAD1015-1050-6 SUITS CONDUCTOR

**DEADEND**

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
7/3.40	AAC/AAAC	10.20	RIGHT HAND




### TECHNICAL SPECIFICATIONS:

**CATALOGUE NUMBER:** FAD1015-1050-6  
**DESCRIPTION:** FULL-TENSION ALUMINIUM DEADEND  
**MATERIAL:** ALUMINIUM ALLOY  
**NUMBER OF RODS:** 5  
**ROD DIAMETER:** 2.95mm  
**OVERAL LENGTH:** 680mm  
**END FINISH:** CHAMFERED  
**FITTING LAY DIRECTION:** RIGHT HAND  
**COLOUR CODED:** BLUE

### PRODUCT LABEL



### BOX LABEL



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.

LOC							IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE	IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm: ±1.5mm. DIMENSIONS OVER 30mm: ±5% UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5°	TCPN -	PART Alias UTX/DUL FAD1015-1050-6	TITLE FULL-TENSION ALUMINIUM DEADEND (FAD) FITTING COND. RANGE: Ø10.15-Ø10.50 7/3.40 AAC/AAAC					
DIST	—	I	NEW RELEASE	10-05-2013	RN	AT	MATERIAL DESC ALUMINIUM ALLOY	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO -	Cat No FAD1015-1050-6	DRAWN RN	DATE 10-05-2013	TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia		
POS	REV	REVISION RECORD		DATE	DWN	APVD	MATERIAL NO -	MATL SPEC/STD/DRG NO -	PROCESS SPEC HEAT TREAT/PLATING NO -	SIZE A3	PROJECTION 3RD ANGLE	SCALE NTS	DRAWING NO FAD1015-1050-6-C	SHEET 1	OF 1	REV 1

Format: generic\_m03.au.r1.fm 4

Template: tec\_generic\_a3\_metric.au.r1.drw 3

Dwg No from P1 Mod Fam Tbl: 2 >AUXXXXX