



BOILER PROBE WITH INTEGRATED CONNECTOR

SPECIFICATIONS

- Robust, compact design
- Improved overall reliability
- Fast response time
- Integrated connector
- RoHS Compliant

FEATURES

- Suitable for measuring water temperature in various boiler systems
- Standard industry style connector
- Available in a variety of thread types
- Custom tolerances available on request
- Available in range of R/T curves
- Temperature range -40°C to +125°C
- Other RTD elements available (Platinum, Nickel)

APPLICATIONS

- Temperature measurement of water in Hot Water Boiler systems
- Industrial process control
- Boiler control

This assembly consists of a NTC thermistor soldered to an industry std 2.5mm connector. The sensor is assembled into a Brass screw in Housing. Device is available in a variety of thread types.

BOILER PROBE WITH INTEGRATED CONNECTOR

PERFORMANCE SPECS

| Parameters | Units | Value |
|-------------------------------|---------|-------|
| Nominal Resistance at +25°C | Ohms | 10000 |
| Tolerance from +25°C to +85°C | °C | ±1 |
| Beta Value 25/85 | K | 3976 |
| Tolerance on Beta Value | % | ±1 |
| Time response in still water | Seconds | <8 |

MECHANICAL DETAILS




Figure 1: Boiler probe integrated connector – mechanical drawing

BOILER PROBE WITH INTEGRATED CONNECTOR

RESISTANCE V TEMPERATURE TABLE

| Temp °C | Ohms |
|---------|------|
|---------|------|

| | |
|-----|--------|
| -40 | 336098 |
| -39 | 314553 |
| -38 | 294524 |
| -37 | 275897 |
| -36 | 258563 |
| -35 | 242427 |
| -34 | 227398 |
| -33 | 213394 |
| -32 | 200339 |
| -31 | 188163 |
| -30 | 176803 |
| -29 | 166198 |
| -28 | 156294 |
| -27 | 147042 |
| -26 | 138393 |
| -25 | 130306 |
| -24 | 122741 |
| -23 | 115661 |
| -22 | 109032 |
| -21 | 102824 |
| -20 | 97006 |
| -19 | 91553 |
| -18 | 86439 |
| -17 | 81641 |
| -16 | 77138 |
| -15 | 72911 |
| -14 | 68940 |
| -13 | 65209 |
| -12 | 61703 |
| -11 | 58405 |
| -10 | 55304 |
| -9 | 52385 |
| -8 | 49638 |
| -7 | 47050 |
| -6 | 44613 |
| -5 | 42317 |
| -4 | 40151 |
| -3 | 38110 |
| -2 | 36184 |
| -1 | 34366 |
| 0 | 32651 |
| 1 | 31031 |

| Temp °C | Ohms |
|---------|------|
|---------|------|

| | |
|----|-------|
| 2 | 29500 |
| 3 | 28054 |
| 4 | 26687 |
| 5 | 25395 |
| 6 | 24172 |
| 7 | 23016 |
| 8 | 21921 |
| 9 | 20885 |
| 10 | 19903 |
| 11 | 18973 |
| 12 | 18092 |
| 13 | 17257 |
| 14 | 16465 |
| 15 | 15714 |
| 16 | 15001 |
| 17 | 14324 |
| 18 | 13682 |
| 19 | 13073 |
| 20 | 12493 |
| 21 | 11943 |
| 22 | 11420 |
| 23 | 10923 |
| 24 | 10450 |
| 25 | 10000 |
| 26 | 9572 |
| 27 | 9165 |
| 28 | 8777 |
| 29 | 8408 |
| 30 | 8056 |
| 31 | 7721 |
| 32 | 7402 |
| 33 | 7097 |
| 34 | 6807 |
| 35 | 6530 |
| 36 | 6266 |
| 37 | 6014 |
| 38 | 5774 |
| 39 | 5544 |
| 40 | 5325 |
| 41 | 5116 |
| 42 | 4916 |
| 43 | 4724 |

| Temp °C | Ohms |
|---------|------|
|---------|------|

| | |
|----|------|
| 44 | 4542 |
| 45 | 4367 |
| 46 | 4200 |
| 47 | 4040 |
| 48 | 3887 |
| 49 | 3741 |
| 50 | 3601 |
| 51 | 3467 |
| 52 | 3339 |
| 53 | 3216 |
| 54 | 3098 |
| 55 | 2985 |
| 56 | 2877 |
| 57 | 2773 |
| 58 | 2674 |
| 59 | 2579 |
| 60 | 2487 |
| 61 | 2399 |
| 62 | 2315 |
| 63 | 2234 |
| 64 | 2157 |
| 65 | 2082 |
| 66 | 2011 |
| 67 | 1942 |
| 68 | 1876 |
| 69 | 1813 |
| 70 | 1752 |
| 71 | 1693 |
| 72 | 1637 |
| 73 | 1582 |
| 74 | 1530 |
| 75 | 1480 |
| 76 | 1432 |
| 77 | 1385 |
| 78 | 1341 |
| 79 | 1298 |
| 80 | 1256 |
| 81 | 1216 |
| 82 | 1178 |
| 83 | 1141 |
| 84 | 1105 |
| 85 | 1070 |

| Temp °C | Ohms |
|---------|------|
|---------|------|

| | |
|-----|------|
| 86 | 1037 |
| 87 | 1005 |
| 88 | 974 |
| 89 | 945 |
| 90 | 916 |
| 91 | 888 |
| 92 | 862 |
| 93 | 836 |
| 94 | 811 |
| 95 | 787 |
| 96 | 764 |
| 97 | 741 |
| 98 | 720 |
| 99 | 699 |
| 100 | 678 |
| 101 | 659 |
| 102 | 640 |
| 103 | 622 |
| 104 | 604 |
| 105 | 587 |
| 106 | 571 |
| 107 | 555 |
| 108 | 539 |
| 109 | 524 |
| 110 | 510 |
| 111 | 496 |
| 112 | 482 |
| 113 | 469 |
| 114 | 457 |
| 115 | 444 |
| 116 | 432 |
| 117 | 421 |
| 118 | 410 |
| 119 | 399 |
| 120 | 388 |
| 121 | 378 |
| 122 | 368 |
| 123 | 359 |
| 124 | 350 |
| 125 | 341 |

BOILER PROBE WITH INTEGRATED CONNECTOR

ORDERING INFORMATION

| Part Number | Description | Ω @25°C | MOQ |
|-------------|---|----------------|--------|
| 10K3D1037 | Immersion Probe with Integrated Connector | 10000 | 10000* |

* For quantities less than Minimum Order Quantity – Contact Distribution

NORTH AMERICA

Measurement Specialties, Inc.,
a TE Connectivity Company
1711 139th Lane NW
Andover, MN 55304
Tel: +1 763 689 4870
Fax: +1 763 689 5033
customer care.ando@te.com

EUROPE

Measurement Specialties (Europe), Ltd.,
a TE Connectivity Company
Ballybrit Business Park
Galway Ireland
Tel : +353-91-753238
Fax : +353-91-770789
Email: customer care.glw@te.com

ASIA

Measurement Specialties (China), Ltd.,
a TE Connectivity Company
No. 368 Wulian 1st Road
Gongxing Town
Shuangliu, Chengdu
Sichuan, 610200
China
Tel: +86 (0) 28 8573 9088
Fax: +86 (0) 28 8573 9070
Email: customer care.chdu@te.com

te.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.