


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
D1		REVISED PER ECN-24-273565	02JUL2024	MM	LR



PART NUMBER	"A" THREAD	ØB ±.02	ØC REF	ØJ		P REF REC	T REF	PANEL THK ⁴
				MIN EXP	MAX REC			
CES-2-F1A-XX	1-12 UNF	.75 [19,05]	1.41 [35,82]	.40 [10,16]	.11 [2,79]	2.25 [57,15]	.21 [5,33]	1/4 [6,35]
CES-2-F1-XX	1-12 UNF	.75 [19,05]	1.41 [35,82]	.60 [15,24]	.17 [4,31]	2.75 [69,85]	.21 [5,33]	1/4 [6,35]
CES-3-F1-XX	1 3/8-12 UNF	1.10 [27,94]	1.91 [48,52]	.60 [15,24]	.17 [4,31]	2.75 [69,85]	.31 [7,88]	1/4 [6,35]
CES-4-F1-XX	2-8 UN	1.56 [39,62]	2.72 [69,09]	.90 [22,86]	.30 [7,62]	3.15 [80,01]	.31 [7,88]	3/8 [9,65]
CES-5-F4-XX	3 3/8-8 UN	2.90 [73,66]	4.10 [104,14]	1.25 [31,75]	.50 [12,7]	4.50 [114,30]	.31 [7,88]	1/2 [12,7]

NOTES:

1. THE LAST "XX" IN THE PART NUMBER DESIGNATES MATERIAL AS SHOWN BELOW:
 "AL": ALUMINUM 6061 T-6 WITH FINISH OF HARD ANODIZE PER MIL-A-8625, TYPE III, CLASS 2, DYED BLACK.
 "SS": STAINLESS STEEL TYPE 316, WITH FINISH OF PASSIVATE PER QQ-P-35, OR MIL-S-5002 FOR STANDARD BLACK NYLON MATERIAL, OMIT THE LAST "XX" IN THE PART NUMBER.
2. HEAT SHRINKABLE BOOT MATERIAL IN ACCORDANCE WITH -3 POLYOLEFIN
3. PART TO BE MARKED AS SHOWN, REPLACE X'S WITH APPROPRIATE CHARACTERS. (IE: CES-3-F1-AL).
4. THIS PART IS DESIGNED TO FIT THROUGH A BULKHEAD OR PANEL WITH A MAXIMUM WALL THICKNESS AS INDICATED IN TABLE.
5. FACTORY APPLIED HOT MELT ADHESIVE IS STANDARD. /97 HOT MELT ADHESIVE S1297

TE Connectivity. All Rights Reserved. © 2024

DIMENSIONS: INCHES	DWN	02JUL2024	MATERIAL	-	FINISH	-
	CHK	02JUL2024				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	02JUL2024				
	PRODUCT SPEC	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± -	APVD	02JUL2024	A4	06090	©= CES-X-FX-XX	-
1 PLC ± -	PRODUCT SPEC	-	WEIGHT	0.000000	CUSTOMER DRAWING	SCALE DNS
2 PLC ± -	APPLICATION SPEC	-	SHEET 1 OF 1			REV D1
3 PLC ± -	APVD	02JUL2024	CUSTOMER DRAWING			
4 PLC ± -	PRODUCT SPEC	-	SCALE DNS			
ANGLES ± -	APVD	02JUL2024	SHEET 1 OF 1			