





REVISION					
ZONE	LTR	ECN	DESCRIPTION	DATE	APPROVED
	C	38802	GENERAL DWG UPDATE	1/19/99	me




DETAIL B

7-1532141-1

NOTES: UNLESS OTHERWISE SPECIFIED

1. MARK PER TIS.
- ⚠ POTTING COMPOUND USED IS 194-8102-6215/6225.
3. INSTALL FLOAT BUSHING(096-0019-0001) ON CONNECTOR AS SHOWN.
- ⚠ EPOXY WICKING: UNINSULATED WIRE : .050 MAX
INSULATED WIRES UP TO #25 AWG : .125 MAX
INSULATED WIRES #24 AWG OR LARGER : .200 MAX
5. CRIMP LEADS INTO CONTACTS PER MEP 302-05.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCE ARE:		APPROVALS		 MICRODOT CONNECTORS A DIVISION OF UNI-STAR INDUSTRIES INC. 306 PASADENA AVE., SO. PASADENA, CA 91030	PROD CODE 845
FRACTIONS	DECIMALS	ANGLES	SIGNATURE		
± 1/8	.XX ± .01 .XXX ± .005	± 2°	DRAWN BY MEL F. CAMPOS P.E. <i>Mel Campos</i> M.E. <i>Mel Campos</i> D.A.	04/14/99	METAL SHELL 'D' CONNECTOR MCK-***-F-***S
MATERIAL:	FINISH:		THIS DOCUMENT IS THE PROPERTY OF MICRODOT CONNECTORS, A DIVISION OF UNI-STAR INDUSTRIES INC. USE OF THIS DOCUMENT OR ANY PART THEREOF IS STRICTLY FORBIDDEN WITHOUT THE EXPRESS WRITTEN PERMISSION OF MICRODOT CONNECTORS, A DIVISION OF UNI-STAR INDUSTRIES INC.		
		SIZE	CODE IDENT NO.	DRAWING NO.	
		A	98278	094-0000-0010	
		SCALE: NONE			SHEET 1 OF 1