
THIS DRAWING AND THE INFORMATION SET FORTH HERE-ON ARE THE PROPERTY OF TYCO ELECTRONICS AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE, OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY TYCO ELECTRONICS IS PROHIBITED. REVISIONS **APPROVED** DESCRIPTION DATE 6-29-18 НΑ OBS PER ECO 18-000682

NOTES:

- 1. PACKAGE: 500 FEET PER REEL.
- 2. LENGTH TOLERANCE: $\pm 2\%$
- 3. WHEN INSTALLED IN DIRECT CONTACT WITH FLAT CONDUCTOR CABLE, SURFACE TRANSFER IMPEDANCE LEVEL IS APPLICATION DEPENDENT.
- 4. THIS PRODUCT IS DESIGNED TO MEET THE REQUIREMENTS OF TYCO ELECTRONICS/RAYCHEM SPECIFICATION C-6119, QUALIFICATION IS PENDING.
- 5. SEE PAGE #2 FOR SPECIFIC CUSTOMER'S FOLDING REQUIREMENTS PRIOR TO EACH SHIPMENT.



Raychem MTC

©2010-2011 Tyco Electronics. All rights reserved.					C	USTOMER	DRAWI	NG	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. METRIC DIMENSIONS ARE IN BRACKETS. DECIMALS .XXX ± .010 [mm] .XX ± .03 [mm] ANGLES	DRAWN	ZS.O.	Feb/1/2010	Tyco Electronics 300 Constitution Drive					
	CHECKED				= / =		stitution Drive CA 94025 U.S	S.A	
	APPROVED			TITLE	INCH WIDF			Г	
	APPROVED	M.HIGGY	Feb/1/2010		1 INCH WIDE SHIELD FOR FLAT CABLE, COPPER—POLYIMIDE				
	CHA-0049CS2982			LAMINATE, 2 SIDES					
.X — ± —				SIZE	CAGE CODE:	DWG. NO.		REV	
WEIGHT:	THIRD ANGLE PROJECTION			06090	CHA-0049	CS2982	\Box		
2.87g(0.0063 Lbs) / ft. MAXIMUM	11.002011011			SCALE	: NONE		SHEET 1 OF 2		

Fold Endurance

5.1 Test Procedure and Acceptance:

7 samples at 6 inch length each of the shield material shall be used for performing this folding test. The sample shall be folded at a right angle as shown in Figure 1 and placed on horizontal surface between two smooth surfaced flat metal plates.

A load (weight/force) of 30 ± 1 lbf/in2 shall be placed over the triangular area of the fold for a 15 minute duration. The specimen shall then be unfolded and the equivalent load applied to the unfolded, creased portion of the specimen for 15 minutes. This cycle of folding and unfolding shall be repeated once more, with the fold at the same place and in the same direction.


5.2 Inspection Criteria at the Folded Area

The specimen shall then be inspected at the folding area using the naked eye for evidence of cracks or delamination of the Polyimide layer and copper layer. There shall be no evidence of cracks or delamination of the Polyimide layer and copper layer. Delamination will be cause for rejection.

Stretching of the Polyimide layer, at the fold line characterized by an opaque line is acceptable as long as the width of the opaque line does not exceed 0.020 inches in width, see figure 2.

5.3 Inspection Criteria Outside the Folded Area:

The specimen shall be inspected for interior voids and delamination outside the folding area. The total areas of any evidence of Interior voids, or delamination between the Polyimide layers and copper layer should not exceed 0.001 inch square in an area of one inch square of the shield material. Otherwise the material will be rejected.








Fig 2

Raychem MTC PRODUCTION DRAWING

THIRD ANGLE **PROJECTION**

CAGE CODE: SIZE 06090

SCALE: NONE

DWG. NO. CHA-0049CS2982 REV

ZS.O. Feb/1/2010

DRAWN