



SOLUTIONS FOR MILITARY MARINE

FOR SURFACE SHIPS AND SUBMARINES . . . SPACE-SAVING, PERFORMANCE-ENHANCING ELECTRICAL INTERCONNECTS, CABLES, AND POWER MANAGEMENT THAT KEEP THE FLEET ON STATION



Seaworthy solutions

Launch with Mission-Critical Reliability

Supporting the Mission with Powerful Solutions

The sea is a harsh environment, ever challenging the electrical and electronic systems that control naval vessels. With our deep understanding of the unique needs of marine environments, TE Connectivity (TE) has a proud history of providing solutions to make ships more reliable, more sophisticated, and mission ready. Our solutions save weight, require less space, and help you

achieve new levels of performance. Whether it's processing-intensive target acquisition or reliable delivery of power, you'll find more choice of seaworthy products to support the mission undersea, in littoral waters, or across the expanses of oceans.

Typical Applications

- Main Guns
- Close-In Weapon Systems
- Missile Systems
- Torpedo Systems

DEUTSCH DTS AND 602 BRONZE CONNECTORS

DTB threaded connectors are MIL-DTL-38999 Series III style and STD CECC 75201-002 styles, but feature a bronze shell and sealing for harsh marine environments. The 602/RR Series are medium-density bayonet-coupling connectors. They include styles and layouts qualified to Pattern 602 and are interchangeable with MIL-DTL-26482 Series II connectors. An aluminium-bronze option is designed specifically for naval applications



RECTANGULAR CONNECTORS

A full line of rack-and-panel connectors support power, signals, RF and optics in modular high-density rectangular connectors for easier "black-box" installation and removal of LRUs and similar equipment. Along with a full range of high-speed backplane connectors, we support speeds of 10+ Gb/s and provide reliability in marine environments





Solutions for Weapons Systems

High-Speed Connectors

- High-Speed Electrical and Optical I/O Connectors
- High-Speed Backplane Connectors

High-Performance Connectors

- Rack and Panel Connectors
- Circular Mil-Spec Connectors
- RF Connectors
- Rugged Optics

Relays and Contactors

- High-Performance Relays and Contactors
- Motor Drive Relays

Wire and Cable

- Zero-Halogen Wire and Cable
- Multiconductor Cable
- Harnessing Components

MOTOR DRIVE RELAYS

Even under extreme conditions, MDR relays give chatter-free operation. The 10 A rotary relays are available with up to 24 poles, AC or DC coils, and latching and nonlatching styles to meet the needs necessary for high-reliability operation in challenging applications



DEUTSCH DBAS SERIES 81703 CONNECTORS

A rugged connector with push-pull coupling, the DBAS Series offers easy and secure locking. The coupling ring is free to rotate, providing a unique feel-control check for 100% mating. With a temperature rating from -55°C to +200°C, the connectors are available in environmentally or hermetically sealed, rack-mountable, and lanyard release versions



SEACON CABLE ASSEMBLIES

Integrated harnesses provide ready-to-install solutions that mean reliability in the toughest application environments. Every assembly meets your requirements for sealing, pressure proofing, moisture and chemical resistance, shielding, strain relief, flexibility, and ease of use



Rely on High-Performance Power Control

Connecting Vessels with Rugged Performance

We offer relays and contactors with make/break current ratings up to 2000 A, current ratings up to 1000 A at 28 VDC and 500 A at 900 VDC, and hermetic sealing for reliability. Our relays offer an industry-leading combination of high-current switching in compact, lightweight packages.

Power cables and connectors are designed to carry power efficiently, with lower resistance and less bulk.

Our power solutions may help combat the potential hazards of naval applications, resisting salt, moisture, harsh oils, fuels, and other solvents and maintaining efficient power distribution under tough conditions of vibration and shock.

Typical Applications

- Power Distribution Racks
- Load Centers
- Automatic Bus Transfers
- Motor Controllers
- Hybrid Electric Propulsion

DEUTSCH RACK AND PANEL POWER SUPPLY CONNECTORS

Designed for battery racks, CSR 31000 Series connectors offer two main power contacts—with ratings of 350 or 500 A—and zero or seven pilot contacts. The fixed socket and floating plug arrangement offers generous misalignment tolerances for easy mating



RAYCHEM HIGH-VOLTAGE TERMINATION KITS

For a long service life at ratings of up to 35 kV, termination kits offer an insulating surface that can withstand long-term stress and surface pollution. Load cycle testing verifies the long-term compatibility between the termination system and the cable



RAYCHEM ZERO-HALOGEN POWER CABLES

Safer power is possible by reducing or eliminating toxic emissions in the event of a fire. Our lightweight zero-halogen power cables accommodate both primary and secondary power needs in a rugged cable





Solutions for Power Connectors

Connectors

- Power Connectors

Wire and Cable

- Zero-Halogen Wire and Cable
- Power Cables

Relays and Contactors

- High-Performance Relays and Contactors
- Power Distribution Units
- Motor Drive Relays

High Voltage

- High-Voltage Relays
- High-Voltage Termination Kits

DEUTSCH DTS-HC SERIES CONNECTORS

Ideally suited for high-power interconnections in harsh environments, the connector's power contacts are rated to 300 A and are suitable for terminating conductors up to 70 mm². Based on proven military standard 38999 housings, the connectors provide the reliability and performance required for the most demanding military and aerospace applications



HIGH-VOLTAGE DC CONTACTORS

TE delivers the switching performance demanded for marine, aerospace and defense applications with our lightweight contactors, which offer continuous current ratings up to 500 A at 900 VDC in very compact sealed packages. Custom-designed main power and high-voltage distribution assemblies are also available



Smarter Connectivity for Intelligent Communications

Increasing Capability in Communications Systems

The increasing sophistication and importance of communication systems demand more processing power and more bandwidth. Equally important is miniaturization to pack more processing power into smaller spaces. We offer a wide range of high-density, high-speed connectors to enable high speeds from the backplane to the I/O.

Typical Applications

- Combat Systems
- Fire Control
- Machinery Control
- C4 Processors
- Radio Systems
- Radar

EMBEDDED COMPUTING CONNECTORS

Achieve complete high-speed, high-density interconnections for VPX embedded computing with MULTIGIG RT connectors for VITA 46, Mezalok mezzanine connectors for VITA 61, MULTI-BEAM XLE power connectors for VITA 62, and optical and RF modules for VITA 66 and 67



FIBER-OPTIC CONNECTORS

Count on support for optical connectivity—for vibration-tolerant expanded beam, high-performance ceramic ferrule, or high-density MT ferrule-based interconnections. We offer fiber-specific connectors and termini for a range of Mil-Spec circular and rectangular connectors



RF CABLE AND CONNECTORS

We provide a wide range of coaxial connectors for the defense industry including military-qualified SMA, BNC and TNC connectors along with a portfolio of small form factor high-frequency connectors





Solutions for Radar and Communications

Embedded Computing

- High-Speed I/O Connectors
- High-Speed Backplane Connectors
- Optical and RF Modules

Mil-Spec Connectors

- Circular Connectors
- RF Connectors
- Rugged Optics
- High-Voltage Connectors

Wire and Cable

- Controlled Electrical Cables
- Zero-Halogen Wire and Cable
- High-Speed Networking Cable

Relays and Contactors

- High-Voltage Relays
- Lightweight AC/DC Relays and Contactors
- Motor Drive Relays
- Signal Relays

CEELOK FAS-X CONNECTORS

Using a 38999-style shell, CeeLok FAS-X connectors handle speeds of 10 Gb/s and more, making them an ideal choice for 10G Ethernet, IEEE 1394, USB 2.0 and other protocols. The termination and assembly is fast and straightforward, allowing field terminate and repair in as little as 5 minutes



POLAMCO BACKSHELLS

Our newest line offers a complete range of high-performance backshells for unshielded, shielded, and rugged conduit systems. Supporting one of the widest variety of Mil-Spec and COTS connectors, we have a solution for rugged, lightweight, and specialized needs



9316 SERIES CONNECTORS

A workhorse family for a wide range of on-ship and off-ship applications, immersible 9316 connectors are available in seven stainless steel shell sizes for power, signal, coaxial, and optical contacts. The connectors are available with a range of voltage, current, and temperature ratings, with a pressure rating to 10,800 psi, and hermetic versions



Build in Reliability from Bow to Stern

Boosting Performance with Powerful Infrastructure Solutions

We support the complete infrastructure of naval craft, from power to communications and from networks to electrical systems. You will find cables with reduced size and weight, sealed relays and contactors, and a wide assortment of products to help manage and identify cables and subsystems. Marine-grade heat-shrink tubing, identification products,

grounding and wire termination, and sealed bulkhead feed-throughs are just a few examples of products that can help build a reliable, maintainable infrastructure.

Typical Applications

- Cable Management Systems
- Electrical/Control Panels
- Lighting Systems
- Voice/Video Systems
- Feed-Through Panels
- Hull Penetrators
- Sonar Assemblies

SEACON PENETRATORS

Our range of pressure-tested penetrators spans the needs of submarines, surface ships, and unmanned underwater vehicles—from hulls to compartmentalization. With support for signals, power, and optics, penetrators are available in standard and custom configurations to meet specific requirements for pressure, contact configurations and density, and service life



DEUTSCH 901 SERIES CONNECTORS

With a strong coupling system to resist harsh environmental and mechanical challenges, these rugged connectors are designed in accordance with ABG/T 538 standards



COMPOSITE ENCLOSURES

Custom-made enclosures using advanced composites have excellent impact resistance and strength, but are significantly lighter to save critical weight. Plus they can offer EMI shielding, custom circuits and contacts, embedded antennas, and other features





Solutions for Hull Systems

Connectors

- Pressure-Proof Connectors
- Penetrators

Wire and Cable

- Custom Marine Cables
- Multiconductor Cables
- Zero-Halogen Wire and Cable

Harnessing

- Zero-Halogen Tubing, Boots and Transitions
- Gel-filled Sealing Boots
- Glands
- Anti-Corrosion Sealing Sleeves
- Shield Termination and Grounding Kits

SUBMARINE NAVIGATION LIGHTS

We design a variety of lights qualified to MIL-DTL-24560 for shipboard navigation, signal, and warning lights suited to both surface and subsea applications. Submarine lights use tempered glass Fresnel globes to enhance light output, increase impact resistance, and withstand discoloration and etching at sea



RAYCHEM MULTICONDUCTOR CABLE

Our expertise in advanced materials yields wire and cable that's smaller, lighter, and tougher than traditional counterparts, with wide temperature ranges, resistance to fuels, salt water and contaminants, and options for EMI/EMP shielding. They also offer the flexibility to route through tight spaces and sharp turns



Go the Distance with High Performance On Ship or Off

Strengthening Cable Reliability Through Innovation

Towed array sonar and similar applications require tough cables. Supporting both shallow and deep towing, we offer steel-armored cables capable of withstanding depths up to 6000 meters with concentric stranded conductors and ruggedized optical packages for harsh environments. The cables provide the strength and low rotation required for high-speed towing.

We offer a wide range of configurations—available in both standard and custom versions—supporting power, multiconductor, coaxial, and optical needs for power, instrumentation, video and any other applications. And we excel at producing cables that are smaller and lighter without sacrificing performance.

Typical Applications

- Processors
- Receivers
- Transmitters
- Towed Arrays

ELECTRICAL PANELS

Our electrical panels for communications, testing, and power distribution are built to meet MIL-STD-461 EMC and MIL-S-901 shock requirements. They feature heavy-gauge construction and shielding to create rugged panels that will neither interfere with sensitive electronics nor be susceptible to outside EMI



ROCHESTER AND RAYCHEM SONAR DIPPING CABLE

Naval organizations throughout the world rely on both Raychem and Rochester Cable branded products for applications including submarine towed array cables, helicopter dip sonar cables and electro-optical cables for ROV salvage and recovery



SEACON PROXIMITY SWITCHES

Pressure-tested and hermetically sealed magnetic proximity switches, which are commonly used to indicate mast and antenna position, withstand pressures as high as 10,000 psi. The rugged switches offer high cycle lives to provide a rugged solution





Solutions for Sonar

Connectors

- Dry-Mate Connectors
- Wet-Mate Connectors
- High-Speed Connectors
- Rugged Optics

Wire and Cable

- Sonar Dipping Cables
- Towed Array Cables
- Umbilical Cables

Complete Cable Assemblies

SEACON AND DEUTSCH UNDERWATER CONNECTORS

Wet-mate or dry-mate, our pressure-tested connectors withstand the pressures and harsh environment of underwater applications



ROCHESTER TOWED ARRAY CABLES

Designed for and successfully deployed in the most hostile environments, our towed array cables, available with both copper systems and state-of-the-art electro-optic systems, feature custom armoring and steel-armored optical elements to achieve extended life



Empower Engineers to Solve Problems, Moving the World Forward.

AMP | AGASTAT | CII | DEUTSCH | DRI | HARTMAN | KILOVAC
MICRODOT | NANONICS | POLAMCO | Raychem | Rochester | SEACON

CONNECT WITH US

We make it easy to connect with our experts and are ready to provide all the support you need. Visit te.com/support to chat with a Product Information Specialist.

QUALITY STARTS WITH THE RIGHT APPLICATION TOOLING

Creating a quality crimp connection is essential to delivering high performance and reliability in extreme environments. From low to high volume wire processing, TE has you covered with a full range of application tooling and a global field service team.

- [View all application tooling](#)
- [Connect with our experts to find the right tool for your application](#)

te.com/MilitaryMarine

AMP, AGASTAT, CeeLok FAS-X, CII, DEUTSCH, DRI, HARTMAN, KILOVAC, Mezalok, MICRODOT, MULTI-BEAM, MULTIGIG RT, NANONICS, POLAMCO, PRO BEAM, Raychem, Rochester, SEACON, TE, TE Connectivity, and TE connectivity (logo) are trademarks owned or licensed by TE Connectivity. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

Other products, logos, and company names mentioned herein may be trademarks of their respective owners. Images courtesy of the U.S. Department of Defense without endorsement of products.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

© 2022 TE Connectivity All Rights Reserved.

7-1773447-1 01/22

SOLUTIONS FOR MILITARY MARINE

TE Connectivity
Aerospace, Defense & Marine
2900 Fulling Mill Road
Middletown, PA 17057