





# **DP86** Constant Current With Cable

### **SPECIFICATIONS**

- 316L SS
- Wet/Wet Differential
- Low Pressure
- ◆ 0 100mV Output

The DP86 constant current with cable differential pressure sensor is a double-sided, media compatible, piezoresistive silicon pressure sensor packaged in a 316L stainless steel housing. The DP86 constant current with cable is designed for o-ring mounting. The sensing package utilizes silicone oil to transfer pressure from the two 316L stainless steel diaphragms to a single sensing element.

The DP86 constant current with cable is designed for high performance, low pressure applications where differential pressure measurement is required. The stainless steel package makes it suitable for use in liquids and corrosive environments.

Please refer to the DP86, uncompensated, non-silicone oil, constant current and constant voltage (fittings and cable design) for more information on different features of the DP86

# FEATURES

O-Ring Mount Up to -40°C to +125°C Operating Range Up to ±0.1% Pressure Non Linearity Solid State Reliability Low Pressure

## **APPLICATIONS**

Level Controls Tank Level Measurement OEM Equipment Corrosive Fluids and Gas Measurement Systems Flow Measurements

## STANDARD RANGES

Range	psid	Range	bard
0 to 1	•	0 to .07	•
0 to 5	•	0 to .35	<b></b>
0 to 15	•	0 to 001	•
0 to 30	<b></b>	0 to 002	<b></b>
0 to 50	•	0 to 3.5	•
0 to 100	<b></b>	0 to 007	<b></b>
0 to 300	<b>•</b>	0 to 020	•
0 to 500	•	0 to 035	*

# PERFORMANCE SPECIFICATIONS

### Supply Current: 1.5mA

Ambient Temperature: 25°C (unless otherwise specified)

	≤005PSI				≥015PSI			NOTEO		
PARAMETERS	MIN	ТҮР	MAX	MIN	ТҮР	MAX	UNITS	NOTES		
Span	50	100	150	75	100	150	mV	1		
Zero Pressure Output	-2.0	0	2.0	-1.0	0	1.0	mV	2		
Pressure Non Linearity	1psi: -0.30 to 0.30 5psi: -0.20 to 0.20			-0.10		0.10	%Span	3		
Pressure Hysteresis	-0.10	±0.02	0.10	-0.05	±0.02	0.05	%Span			
Repeatability		±0.02			±0.02		%Span			
Accuracy RMS of NL, HY, RP		±0.6	±1.0		±0.6	±1.0	%Span			
Input Resistance	2000	3500	5800	2000	3500	5800	Ω			
Output Resistance	4000		30000	4000		25000	Ω			
Temperature Error – Span	-1.5		1.5	-1.0		1.0	%Span	4		
Temperature Error – Offset	-2.5		2.5	-1.0		1.0	%Span	4		
Thermal Hysteresis – Span	-0.25	±0.05	0.25	-0.25	±0.05	0.25	%Span	4		
Thermal Hysteresis – Offset	-0.25	±0.05	0.25	-0.25	±0.05	0.25	%Span	4		
Long Term Stability – Span		±0.10			±0.10		%Span/Year			
Long Term Stability – Offset		±0.25			±0.10		%Span/Year			
Line (Common Mode) Pressure			1000			1000	psi			
Line Pressure Effect on Zero		Ipsi: 4.0 Max 5psi: 0.8 Max				0.5	%Span/1Kpsi			
Supply Current	0.5	1.5	2.0	0.5	1.5	2.0	V	5		
Output Load Resistance	5			5			MΩ	6		
Insulation Resistance (50Vdc)	50			50			MΩ	7		
Output Noise (10Hz to 1KHz)		1.0			1.0		uV p-p			
Response Time (10% to 90%)		0.1			0.1		ms			
Pressure Overload		psi: 10X Max 5psi: 3X Max				зХ	Rated	8		
Pressure Burst		psi: 12X Max 5psi: 4X Max				4X	Rated	8		
Compensated Temperature		si: 0°C to 50° si: 0°C to 70°		-20		+85	°C			
Operating Temperature		: -40°C to +8 -40°C to +12		-40		+125	٥C	9		
Storage Temperature	-40		+125	-40		+125	°C	9		
Voltage Breakdown	500V rms @ 50Hz, Leakage Current < 1mA									
Shock	50g, 1msec half sine shock per MIL-STD-202G, Method 213B, Condition A									
Vibration	±20g MIL-STD 810C, Procedure 514.2, Figure 514.2-2, Curve L									
Media – Pressure Port	Liquids and gases compatible with 316/316L Stainless Steel									

#### Notes

1. For amplified output circuits, 3.012V ±1% interchangeability with gain set resistor. See application schematic.

- 2. Measured at ambient.
- 3. Best fit straight line

4. Over the compensated temperature range with respect to 25°C.

5. Guarantees output/input ratiometricity.

6. Load resistance to reduce measurement errors due to output loading.


7. Between case and sensing element.

8. For "H" (high-end) port, rated or 1000psi whichever is less. For "L" (low-end) port rated or 150psi whichever is less. The maximum pressure that can be applied to a transducer without rupture of either the sensing element or transducer.


9. Maximum temperature range for product with standard cable and connector is -20°C to +105°C.


# DIMENSIONS

Dimensions are in inches [mm]




Dimensions are in inches [mm]






# **APPLICATION SCHEMATIC**



### ORDERING INFORMATION



Cable (1 = No Cable on Pin Side, 2 = 1" Cable on Pin Side) Electrical (C = Ribbon Cable with Connector, R = Ribbon Cable) Type (C = Constant Current, Compensated) Fitting (Weldable, No Fitting) Unit (P = psi, B = Bar) Pressure Range Model

#### **NORTH AMERICA**

Measurement Specialties, Inc., a TE Connectivity Company Tel: 800-522-6752 Email: customercare.frmt@te.com

#### EUROPE

Measurement Specialties (Europe), Ltd., a TE Connectivity Company Tel: 800-440-5100 Email: <u>customercare.lcsb@te.com</u>

### ASIA

Measurement Specialties (China), Ltd., a TE Connectivity Company Tel: 0400-820-6015 Email: <u>customercare.shzn@te.com</u>

### TE.com/sensorsolutions

Measurement Specialties, Inc., a TE Connectivity company.

Measurement Specialties, TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2015 TE Connectivity Ltd. family of companies All Rights Reserved.



