



## HEAT-SHRINKABLE WRAPAROUND SLEEVE CRSM FOR CABLE REPAIR AND JOINT OUTER REJACKETING

### KEY FEATURES

- High electrical characteristics to achieve requirements for low voltage applications
- Medium wall, Cross-linked polyolefin. UV stabilized and not reinforced
- Halogen-free material content, non-corrosive and non-toxic smoke in event of fire & free of lead and aluminium
- Available inline coated with hot melt adhesive or uncoated
- Wraparound sleeve used for repair of damaged cable jackets insulation and for re-jacketing of low voltage joints
- Compliant to RoHS and REACH regulations
- Color black, >3 : 1 shrink ratio
- Unlimited shelf-life

TE Connectivity's (TE) Raychem CRSM heat-shrinkable wraparounds are a fast and reliable permanent cable repair and sealing system. The cable repair sleeve is quickly fitted in place by means of its rail and channel closure. A moisture-proof, insulating and tight-fitting repair is then obtained in one step by heating, which makes the sleeve diameter shrink and the inside sealant coating melt, flow and fill the damaged cable area.

The CRSM wraparound sleeves will fit a wide range of different cable diameters. The sealant exhibits excellent bonding and sealing characteristics to all substrates commonly used in the various cable and oversheath constructions, such as polymeric, rubber, lead and aluminium. CRSM wraparounds are made of an abrasion resistant semi-rigid material and are a result of our extensive capability in materials technology.

CRSM are used in low voltage applications for insulation and sealing against moisture of cable joints and in low and medium voltage applications for sealing and mechanical protection, for outer re-jacketing and for cable repair.

The material content of the CRSM tubings is halogen-free and stabilized against UV irradiation. CRSM tubings have proven their long-term reliability in harsh climatic conditions. CRSM tubings have an unlimited shelf life when stored under normal conditions.

**Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.**

## Heat-Shrinkable Wraparound Type CRSM



TESTING		
Physical Characteristic	Test Method	Material Requirements
Tensile Strength	ISO 37	14 MPa min
Ultimate Elongation	ISO 37	300% min
Hardness	ISO 868	≥ 50 shore D
Accelerated ageing 7 days at 150°C ± 2°C		
Tensile Strength	ISO 37	12 MPa min
Ultimate Elongation	ISO 37	300% min
Low Temperature Flexibility	ASTM D 2671 Procedure C	No cracking at 4 hours at -30°C ± 3°C
Dielectric Strength	IEC 60243 part 1 and 2	≥ 10 kV/mm min.
Volume Resistivity	IEC 60093	1 x 10 <sup>10</sup> Ω cm min
Water Absorption	ISO 62 method 1	≤ 0.5 % max after 14 days at 23°C ± 2°C
Corrosion	ASTM D2671 Part A	No corrosion after 16h at 150°C
Weathering	The material from which CRSM is manufactured contains carbon black (≥ 2,5 %) to protect it from ultra-violet light	
Application characteristics		
Operating temperature range	- 30°C up to + 100°C	
Shrink ratio	> 3 : 1	
Longitudinal shrinkage free recovered	≤ - 10 %	

PRODUCT SELECTION INFORMATION - DIMENSIONS ARE IN mm						
Description	Application Range		Diameter		Width	
	min	max	Expanded min	Recovered max	Expanded nom	Recoverd min
CRSM 34/10	11	21	35	9	0.3	2.4
CRSM 53/13	17	32	54	15	0.3	2
CRSM 84/20	24	50	86	21	0.3	2
CRSM 107/29	31	65	108	27	0.3	2
CRSM 143/36	33	86	144	28	0.3	1.8
CRSM 198/55	56	120	203	50	0.3	2.1
CRSM 250/98	103	150	257	91	0.4	1.7

All sizes are available in the standard lengths 1000 mm, 250, 500, 750, 1200, 1500 mm. All lengths subject to standard cutting tolerances. TE's Raychem wraparound CRSM are available coated with an inner sealant wall.

[te.com/energy](http://te.com/energy)

©2018 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2254-7/18-EN

Raychem, TE Connectivity and TE Connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

### FOR MORE INFORMATION: TE Technical Support Centers

USA:	+ 1 800 327 6996
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 896 089 903
Spain:	+ 34 916 630 400
Italy:	+ 39 333 250 0915
Benelux:	+32 16 508 695
Russia:	+7 495-790 790 2-200
China:	+ 86 (0) 400-820-6015