




7 CABLE ACCOMMODATION DIMS:
JACKET DIA. --- .110 MAX
DIELECTRIC DIA. --- .057-.070
CENTER CONDUCTOR DIA. --- .009-.020
FOR ENVIRONMENTAL SEAL USE EXTRUDED JACKET

6. FOR ELECTRICAL, MECHANICAL & ENVIRONMENTAL
SPECS SEE MICRODOT CATALOG.

5. .016 D. WIRE HOLE 3 PLACES

4. GOLD PLATE PER MIL-G-45204 TYPE II, CLASS I
OVER COPPER PER MIL-C-14550 CL 4

3. GOLD PLATE PER MIL-G-45204 TYPE II, CLASS I

2. SEE RF-ASMB-II ASSEMBLY INSTRUCTIONS.

1. THIS CONNECTOR MATES WITH ALL 50 Ω GOLDEN
CRIMP, CRIMP SILVER & S-50 JACKS &
RECEPTACLES AS LISTED IN MICRODOT CATALOG.

NOTES: UNLESS OTHERWISE SPECIFIED

					DELETED		12	
	1	1	1	1	003-0861-0001	SEALING SLEEVE	SILICONE RUBBER MIL-R-5847	11
4	1	1	1	1	003-1243-0002	INNER SLEEVE	F.M. BRASS PER QQ-B-626	10
4	1	1	1	1	003-0938-0002	MIDDLE SLEEVE	LEADED COPPER	9
	1	1	1	1	003-1242-0001	CABLE BUSHING	TEFLON PER L-P-403	8
3	1	1	1	1	003-0807-0002	PIN CONTACT	COPPER ALLOY	7
					DELETED			6
5	4	1			003-1235-0004	FERRULE SUB-ASSY NUT-1/4" HEX W/WIRE HOLES		5
4		1			003-1235-0003	FERRULE SUB-ASSY NUT-1/4" HEX.		4
4			1		003-1235-0002	FERRULE SUB-ASSY NUT-1/4" KNURL		3
4				1	003-1235-0001	FERRULE SUB-ASSY NUT-1/4" PARTIAL HEX		2
4	1	1	1	1	003-1239-0002	HOUSING SUB-ASSY		1
	4	3	2	1	COMPONENT			ITEM
	DASH NO. *				No.	NOMENCLATURE	MAT'L & SPEC.	No.

A	3300	RELEASE FOR PRODUCTION	B.T.	4/65	SK	STANDARD TOLERANCES UNLESS OTHERWISE SPECIFIED DEC. $\pm$.015 FRAC. $\pm$ _____ ANGLES $\pm$ _____ ECCENTRICITY MAX. T.I.R. _____ HOLE DIA. $\pm$ _____ SURFACE ROUGHNESS MICRO INCHES THREADS TO MIL-S-7742 COMMERCIAL TOLERANCES APPLY TO STOCK DIMENSIONS	MICRODOT INC. SOUTH PASADENA, CALIF.		
B	9787	UP-DATED 3-4-4 NOS.	S.H.	4/2/65	SK				
C	132-0119-000*	DELETED ITEMS 6 AND 12 ADDED PROD CODE 941 REVISED NOTE 4	DA	5/2/65	SK				
ASSEMBLY		NO REQ'D				SURFACE TREATMENT		NOTED	
NEXT ASSEMBLIES		LET		ECO		MATERIAL		NOTED	
						RT. ANGLE PLUG ENVIRONMENTAL GOLDEN CRIMP 50- Ω		PROD CODE 941	
								DRAWN BY 137	
								SCALE WT DATE	
								10/22/65	
								DRAWING NUMBER	
								CDM 132-0119-000* C	