



## LOOP-IN TERMINALS (LPI) INSULATED WITH SEPARATE FUSE HOLDER DII

### KEY FEATURES

- For application of underground cables up to 35 mm<sup>2</sup> solid and 25 mm<sup>2</sup> stranded
- Degree of protection IP20
- All screws captive
- Minimum pole diameter 90 mm

TE Connectivity's (TE) loop-in terminal LPI sets consist of different, insulated connector blocks with 4 or 6 bores, accepting underground cable wires up to 35 mm<sup>2</sup> solid or 25 mm<sup>2</sup> stranded.

Insulation is made from flame retardant, impact resistant polypropylene. The connectors are suitable for copper and aluminium conductors. The connector blocks are encased in a polypropylene housing, keeping the contact screws captive in any connector position.

Fuse holders are pre-wired, all sets come with a green-yellow earthing cable 16 mm<sup>2</sup> with cable lug for M8 screw.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.



**PRODUCT SELECTION INFORMATION**

| Description                      |   | Part Number |
|----------------------------------|---|-------------|
| <b>Branching Connectors</b>      |   |             |
| <b>GURO-BC4</b>                  | Branching connectors 4 bores (grey)   | CK0309-000  |
| <b>GURO-BC6</b>                  | Branching connectors 6 bores (grey)   | CK0310-000  |
| <b>Set Branching Connectors</b>  |   |             |
| <b>GURO-BCS-4 (99962)</b>        | 3 Branching connectors 4 bores (grey),<br>1 Branching connector 6 bores (grey), Earthing cable H07V-K 16 mm <sup>2</sup><br>(cable lug for M8 screw)  | CK0311-000  |
| <b>GURO-BCS-5 (99963)</b>        | 3 Branching connectors 4 bores (grey),<br>1 Branching connector 4 bores (blue), 1 Branching connector 6 bores (grey),<br>Earthing cable H07V-K 16 mm <sup>2</sup> (cable lug for M8 screw)  | CK0312-000  |
| <b>Fuse holder DII</b>           |   |             |
| <b>GURO-FB-D2 (99964)</b>        | Fuse holder, prewired (black H07V-K 6 mm <sup>2</sup> ), with screw cap (adapter screw<br>and fuse to be ordered separately)  | CK0313-000  |
| <b>GURO-FB-D2-06 (99965)</b>     | Fuseholder, prewired (black H07V-K 6 mm <sup>2</sup> ), complete with adapter screw<br>6A and fuse cartridge 6A   | CK0314-000  |
| <b>GURO-FB-D2-10 (99966)</b>     | Fuseholder, prewired (black H07V-K 6 mm <sup>2</sup> ), complete with adapter screw<br>10A and fuse cartridge 10A   | CK0315-000  |
| <b>Loop-in Terminal sets LPF</b> |   |             |
| <b>GURO-LPF-4-D2 (99967)</b>     | 3 Branching connectors 4 bores (grey), 1 Branching connector 6 bores (grey),<br>Earthing cable H07V-K 16 mm <sup>2</sup> (cable lug for M8 screw), Fuse holder, prewired (black<br>H07V-K 6 mm <sup>2</sup> ), with screw cap (adapter screw and fuse to be ordered separately)   | CK0316-000  |
| <b>GURO-LPF-4-D2-06 (99968)</b>  | 3 Branching connectors 4 bores (grey), 1 Branching connector 6 bores (grey),<br>Earthing cable H07V-K 16 mm <sup>2</sup> (cable lug for M8 screw) Fuseholder, prewired<br>(black H07V-K 6 mm <sup>2</sup> ), complete with adapter screw 6A and fuse cartridge 6A   | CK0317-000  |
| <b>GURO-LPF-4-D2-10 (99969)</b>  | 3 Branching connectors 4 bores (grey), 1 Branching connector 6 bores (grey),<br>Earthing cable H07V-K 16 mm <sup>2</sup> (cable lug for M8 screw) Fuseholder, prewired<br>(black H07V-K 6 mm <sup>2</sup> ), complete with adapter screw 10A and fuse cartridge 10A   | CK0318-000  |
| <b>GURO-LPF-5-D2 (99970)</b>     | 3 Branching connectors 4 bores (grey), 1 Branching connector 4 bores (blue), 1<br>Branching connector 6 bores (grey), Earthing cable H07V-K 16 mm <sup>2</sup> (cable lug for<br>M8 screw) Fuse holder, prewired (black H07V-K 6 mm <sup>2</sup> ), with screw cap (adapter<br>screw and fuse to be ordered separately) | CK0319-000  |
| <b>GURO-LPF-5-D2-06 (99971)</b>  | 3 Branching connectors 4 bores (grey), 1 Branching connector 4 bores (blue), 1<br>Branching connector 6 bores (grey), Earthing cable H07V-K 16 mm <sup>2</sup> (cable lug for<br>M8 screw), Fuseholder, prewired (black H07V-K 6 mm <sup>2</sup> ), complete with adapter<br>screw 6A and fuse cartridge 6A             | CK0320-000  |
| <b>GURO-LPF-5-D2-10 (99972)</b>  | 3 Branching connectors 4 bores (grey), 1 Branching connector 4 bores (blue), 1<br>Branching connector 6 bores (grey), Earthing cable H07V-K 16 mm <sup>2</sup> (cable lug for<br>M8 screw), Fuseholder, prewired (black H07V-K 6 mm <sup>2</sup> ), complete with adapter<br>screw 10A and fuse cartridge 10A           | CK0321-000  |

**FOR MORE INFORMATION: TE Technical Support Centers**

|                   |                      |
|-------------------|----------------------|
| Benelux :         | +32 16 351 731       |
| Canada:           | +1 (905) 475-6222    |
| China:            | +86 (0) 400-820-6015 |
| France:           | +33 3 80 58 3200     |
| Germany:          | +49 (0) 89 60 89 903 |
| Latin/S. America: | +54 (0) 11-4733-2200 |
| Mexico:           | +52 (0) 55-1106-0800 |
| Spain:            | +34 916 630 420      |
| UK:               | +44 0870-8707500     |
| USA:              | +1 (800) 327-6996    |

[te.com/energy](http://te.com/energy)

©2014 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2376-10/14

TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.