

RAYCHEM LOADBREAK ELBOW (ELB-25-210) 25 kV 200A

KEY FEATURES

- Peroxide cured EPDM rubber ensures low tension set and high dielectric strength
- 100% factory production tested for partial discharge and AC Hipot per IEEE 386 Standard
- Capacitive test point provided on elbow
- Fits 25 kV cables up to 250 kcmil
- Molded semiconducting shield provides ground shield continuity in accordance with IEEE 592
- Conforms to IEEE Standard 386

TE Connectivity's (TE's) ELB-25-210 elbows are designed to terminate underground cables to high-voltage apparatus such as transformers and switchgear that are equipped with bushings. They are fully shielded and fully submersible and are designed in accordance to IEEE Standard 386 – latest revision. Loadbreak elbows are designed for use with standard hotstick tools, which allows a loadmake/break operation with a physical disconnect.

They are designed for use on extruded (XLPE or EPR) solid dielectric cable. The conductor range is from #1 AWG to 250 kcmil for aluminum or copper conductors with insulation diameters from 0.370" to 1.060".

This 200A loadbreak elbow includes a copper top compression connector, which connects the cable with the loadbreak probe. Connector is easy to crimp, and suitable for aluminum and copper conductors, and forms a reliable connection.

Optional Integral Jacket Seal

The elbow can be ordered with an integral jacket seal (part number suffix -ES), which is an environmental seal molded to the elbow that prevents moisture ingress.

Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.









RATINGS		
Description	25 kV	
Max Rating Phase-to-Ground	15.2 kV	
Max Rating Phase-to-Phase	26.3 kV	
BIL and Full Wave (Crest)	125kV	
Continuous Current	200 A	
Switching Current	200 A	
Fault-closure Current for 0.17s after 10 Switching Operations	10,000 A symmetrical	

Ordering Formula

ELB-15 1 2 3 4

1	Current Rating Test Point Code	
200 = 200 AMP WITHOUT test point		
210 = 210 AMP WITH test point		

2	Cable Insulator O.D. Range	
Code	Inches	mm
А	.610875	15.5 - 22.2
В	.720985	18.3 - 25.0
С	.920 - 1.185	22.4 - 30.1
D	1.040 - 1.304	26.4 - 33.1

3	Compression Lugs Conductor Size (Aluminum or Copper)		
Code	Str/ Comp	Compact	Solid
2	2	1	1
10	1/0	2/0	2/0
20	2/0	3/0	3/0
30	3/0	4/0	4/0
40	4/0	250	250

4	Jacket Sealing	
Code	Type	
Blank	Blank No Jacket Seal	
ES Integral Jacket Seal		

Elbow Kit Contents:

Elbow body Copper top terminal
Loadbreak probe Probe installation tool


Silicone lubricant Sealing mastic (integral seal only)

Installation instructions sheet

te.com/energy

©2016 TE Connectivity Ltd. family of companies. All Rights Reserved. 6-1773700-4 E481 3/16

Raychem, TE, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.



Related Test Reports

Test Reports: EDR 5581 (25 kV ELB), 5579 (25 kV LRTP/ETP), 5580 (25 kV ELB-BI), Applicable standards: IEEE 386; IEEE 592

FOR MORE INFORMATION: TE Technical Support Centers

USA: +1 (800) 327-6996 Canada: +1 (905) 475-6222 Mexico +52 (0) 55-1106-0800 Latin/S. America: +54 (0) 11-4733-2200 UK: +44 (0) 800-267666 +33 (0) 1-3420-8686 France: Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

