


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F1	NOTE 1 0.76µm PLATING UPDATE (PdNi+AuFLASH)	13JUL2023	BGC	PS

POS.	L±0.5	PART NO.
1	2.54	825434 -1
2	5.08	-2
3	7.62	-3
4	10.16	-4
5	12.70	-5
6	15.24	-6
7	17.78	-7
8	20.32	-8
9	22.86	-9
10	25.40	1-0
11	27.94	1--1
12	30.48	1--2
13	33.02	1--3
14	35.56	1--4
15	38.10	1--5
16	40.64	1--6
17	43.18	1--7
18	45.72	1--8
19	48.26	1--9
20	50.80	2--0
21	53.34	2--1
22	55.88	2--2
23	58.42	2--3
24	60.96	2--4
25	63.50	2--5
26	66.04	2--6
27	68.58	2--7
28	71.12	2--8
29	73.66	2--9
30	76.20	3--0
31	78.74	3--1
32	81.28	3--2
33	83.82	3--3
34	86.36	3--4
35	88.90	3--5
36	91.44	3--6
37	93.98	3--7
38	96.52	3--8
39	99.06	3--9
40	101.60	4--0
41	104.14	4--1
42	106.68	4--2
43	109.22	4--3
44	111.76	4--4
45	114.30	4--5
46	116.84	4--6
47	119.38	4--7
48	121.92	4--8
49	124.46	4--9
50	127.00	5- 825434 -0



- ① MATING SIDE: Min 0.76µm (PdNi + Au FLASH) IN ZONE "F" OVER Min 1.27µm Ni
(Alternative plating - Min 0.76µm Au plating OVER Min 1.27µm Ni)
SOLDER SIDE: 3.0-5.0µm TIN OVER Min1.27µm NICKEL
- ② OBSOLETE

CONTACT PIN	CuZn	⚠
PIN HOUSEING	PBT GV	GREEN
DESCRIPTION	MATERIAL	SURFACE
		COLOR

TE Connectivity. All Rights Reserved. © 2023

DIMENSIONS: mm	DWN A.HO	11APR1984	MATERIAL	-	FINISH	-
	CHK M.SCHAARSCHMIDT	11APR1984	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm	APVD -	-				
0 PLC ± -	PRODUCT SPEC	108-18012	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
1 PLC ± -	APPLICATION SPEC	-	A4	00779	Ⓒ-825434	-
2 PLC ± -	WEIGHT	-	CUSTOMER DRAWING			SCALE
3 PLC ± -						4:1
4 PLC ± -						SHEET
ANGLES ± -						1 OF 1
						REV
						F1