

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
E		LC20-0026-13 / ECO-13-012263	03JUL2013	DM	BJ
E1		LC20-0113-19 / ECO-19-015351	09OCT2019	DM	BJ

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

2 DEADEND ASSEMBLIES ARE FOR VISUAL REPRESENTATION ONLY. NOT PART OF THE BOM AND MUST BE ORDERED SEPERATELY. THIS DWG REPRESENTS DEADEND TAPS ONLY.

3. INHIBITOR IS APPLIED AT FACTORY TO GROOVES OF "C" BODY AND WEDGE.

4 YOKE SIZE IN EACH DEADEND ASSEMBLY [G]. SEE NOTE 2. SEE TABLE.

5 DEADEND TAP ID. MARKED ON WEDGE. SEE TABLE.

		#2 (6/1) 1/0 (6/1) 2/0 (6/1)	#2 1/0 2/0	
M	X-SMALL			1-83843-4
L	XX-LARGE	954 (45/7), (24/7), (54/7), 1033.5 (45/7), (54/7)	1033.5 1113.0	1-83843-3
K	LARGE	397.5 (18/1), (24/7), (26/7)	397.5	1-83843-2
J	X-LARGE	795 (24/7) (26/7), (30/7) (30/19), (54/7)	954	1-83843-1
A	X-SMALL	1/0 (6/1) 2/0 (6/1)	1/0 2/0	1-83843-0
B	SMALL	3/0 (6/1) 4/0 (6/1)	4/0	83843-7
H	X-LARGE	605 (30/19) 636 (26/7) (24/7), (30/19) 666.6 (24/7) (26/7)	715.5, 750, 795	83843-6
G	X-LARGE	477.0 (30/7) 556.5 (24/7) (26/7), (30/7) 605 (24/7) (26/7) 636 (18/1) (36/1)	600, 636, 650, 700	83843-5
F	LARGE	477.0 (26/7) 556.5 (18/1)	556.5	83843-4
E	LARGE	397.5 (18/1) (24/7), (26/7) (30/7) 477.0 (18/1)	450, 477, 500	83843-3
D	SMALL	266.8 (26/7) 336.4 (18/1) (26/7), (30/7)	397.5 336.4, 350	83843-2
C	SMALL	266.8 (18/1)	266.8	83843-1
5	"G" 4	ACSR	AAC	PART NO.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		NAME	
mm [INCH]		0 PLC ± -		M. CHOW	08APR98	TE Connectivity	
		1 PLC ± -		J. HANNA	23APR98	CONNECTOR, REPLACEMENT, DEADEND, AMPACT	
		2 PLC ± -		B. JOHNSON	23APR98	-	
		3 PLC ± -				-	
		4 PLC ± -				-	
		ANGLES ± -				SIZE	CAGE CODE
						A2	00779
						DRAWING NO	RESTRICTED TO
						C=83843	-
MATERIAL	FINISH	WEIGHT	0	CUSTOMER DRAWING	SCALE	NTS	SHEET
						1 OF 1	REV
							E1

1471-9 (1/15)