

Fully flame-retardant, adhesive-lined, polyolefin heat-shrinkable tubing

FL2500 dual wall tubing comprises a tough crosslinked, flame-retardant, polyolefin tubing lined with a new flame-retardant adhesive to provide the optimum solution for applications where full retardancy is preferred, or specified. Rated to 135°C for 3000 hours, it is suitable for use in the automotive harness market and other harsh environments.

FL2500 with its high-performance adhesive lining offers an economical and highly-effective method for permanently sealing and protecting splices, fusible links, terminals, and in-line components. As the tubing is heated and shrinks down onto its substrate, the adhesive lining melts and flows to fill all voids and create a complete seal against moisture, oils, chemicals, etc.

FL2500 is available in a comprehensive range of sizes to meet most component sealing requirements, and is compatible with a wide range of application equipment.

**Temperature rating**


Full recovery temperature:	135°C
Continuous operating temperature	-40°C to 135°C

**Specifications\***

Type	Raychem
FL2500	FL2500 SCD

\*When ordering, always specify latest issue.

**Dimensions (millimeters/inches)**



Size	Inside diameter (including core)		Recovered wall thickness**		W1 (min.) Adhesive wall
	D (min.) Expanded as supplied	d (max.) Recovered after heating	W Total wall	W Recovered wall	
NO. 1	7.62 0.300	1.65 0.065	1.52 ± 0.3	0.060 ± 0.012	0.711 0.028
NO. 2	9.02 0.355	2.29 0.090	1.52 ± 0.3	0.060 ± 0.012	0.711 0.028
NO. 3	11.56 0.455	2.54 0.100	2.29 ± 0.3	0.090 ± 0.012	1.321 0.052
NO. 4	17.79 0.700	4.45 0.175	2.54 ± 0.3	0.100 ± 0.012	1.346 0.053

\*\*Wall thickness will be less if tubing recovery is restricted during shrinkage.

**Ordering information**

Color	Black with a white adhesive liner
Size selection	Consult manufacturer's recommended size selection guidelines.
Standard packaging	Cut pieces. See reverse for standard cut lengths.
Marking	Tubing will be marked with the number size (for example, FL-1, FL-2, FL-3, FL-4).
Ordering description	Specify product name, size, color, and cut length; for example, FL-2500-No. 2-0-50mm (0=Black).

## Specification values

	Property	Unit	Requirement	Method of test
Material	Dimensions	mm ( <i>inches</i> )	See reverse	ASTM D 2671
	Longitudinal change	percent	+0, -10	ASTM D 2671
	Tensile strength*	psi	1500 minimum	ASTM D 2671 Speed 2 in./min.
	Ultimate elongation	percent	300 minimum	ASTM D 2671 Speed 2 in./min.
	Secant modulus* (expanded form)	psi	35,000 minimum	ASTM D 2671
	Concentricity (expanded form)	percent	60 minimum	ASTM D 2671
	Dielectric strength (jacket only)**	volts/mil	500 minimum	ASTM D 149
	Volume resistivity	ohm-cm	10 <sup>13</sup> minimum	ASTM D 257
	Flammability		Self-extinguishing within 30 seconds	SAE J1128 See note below
	Heat shock 4 hours at 250°C		No dripping, flowing, or cracking of jacket	ASTM D 2671
Splice performance	Immersion leak resistance	micro-amps	0.25 maximum	See note below
	Thermal cycling 5 cycles, 5°C to 130°C Followed by test for: Immersion leak resistance	micro-amps	0.25 maximum	See note below
	Thermal aging 168 hours at 130°C Followed by test for: Immersion leak resistance	micro-amps	0.25 maximum	See note below
	Fluid resistance 24 hours at 25°C ± 3°C in: ASTM Reference Fuel C VV-F-800 Diesel Fuel 1 hour at 100°C ± 3°C in: ASTM #3 Oil Followed by test for: Immersion leak resistance	micro-amps	0.25 maximum	See note below
				See note below
				See note below
				See note below

\*Calculate based on wall thickness of jacket only. \*\*Remove adhesive manually prior to testing.  
Note: Consult the FL2500 SCD for specific details about test procedures.

## Standard cut lengths

Part number	Standard cut length	Cut length tolerance
FL2500-No. 1	27mm, 50 mm, 65 mm 1220 mm	± 1.5 mm ± 25.4 mm
FL2500-No. 2	27mm, 50 mm, 65 mm 1220 mm	± 1.5 mm ± 25.4 mm
FL2500-No. 3	27mm, 65 mm, 75 mm 1220 mm	± 1.5 mm ± 25.4 mm
FL2500-No. 4	27mm, 75 mm, 90 mm 1220 mm	± 1.5 mm ± 25.4 mm

Raychem and FL2500 are trademarks of Tyco Electronics Corporation.

**Users should independently evaluate the suitability of the product for their application.**

### Tyco Electronics Corporation

300 Constitution Drive  
Menlo Park, CA 94025-1164  
USA  
Tel: (800) 926-2425 (US & Canada)  
Tel: +1 (650) 361-3860 (All other countries)

Faraday Road  
Dorcan, Swindon, SN3 5HH  
United Kingdom  
Tel: +44 1793 528171

3816 Noborito, Tama-ku  
Kawasaki, Kanagawa 214-8533  
Japan  
Tel: +81 44 900 5102

Asia Pacific Headquarters  
26 Ang Mo Kio, Industrial Park 2  
Singapore 569507  
Tel: +65 4866 151

All information, including illustrations, is believed to be reliable. Users, however, should independently evaluate the suitability of each product for their application. Tyco Electronics Corporation makes no warranties as to the accuracy or completeness of the information, and disclaims any liability regarding its use. Tyco Electronics Corporation's only obligations are those in the Standard Terms and Conditions of Sale for these products and in no case will Tyco Electronics Corporation be liable for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of the product. Tyco Electronics Corporation's Specifications are subject to change without notice. In addition, Tyco Electronics Corporation reserves the right to make changes in materials or processing without notification to the Buyer which do not affect compliance with any applicable specification.

For more information about this product visit [www.tycoelectronics.com](http://www.tycoelectronics.com)