








REVISIONS








P	LTR	DESCRIPTION	DATE	DWN	APVD
E		REVISED PER ECR-24-218282	13SEP2024	LP	DSC


PART NO. BESTELL-NR.	SIZE		RECOMMENDED STRIP LENGTH ABISOLIER-LÄNGE /mm	MINIMUM PULL-OUT SLEEVE STRAND CONDUCTOR MINDEST-AUSZUGSKRAFT HULSE LITZENLEITER /N	COLOUR FARBE 	 $d_1$ /mm	 $d_2$ /mm	$L_1$ /mm	$L_2$ /mm	$s_1$ /mm	 $s_2$ /mm	COLOUR TYPE FARBREIHE DIN/1	PACKAGE QTY VERPACKUNGSEINHEIT PARTS/STÜCK REEL/SPULE
	mm <sup>2</sup>	AWG 											
966 903-2	1.50	16	10.5+0.2	40	BLACK SCHWARZ	1.7+0.25	3.5±0.2	14±1.5	8±0.4	0.15±0.05	0.30±0.10		7100




NOMINAL SIZE NENNGRÖÖE /mm <sup>2</sup>	R /mm
0.5 - 0.75	3.6
1 - 1.5	4.2
2.5	5.0



-  THE AWG CROSS-SECTION CAN DIFFER SLIGHTLY FROM THE DIN-STANDARD CROSS-SECTION VALUES
- 2 NOTE DELETED
-  MAX. INSULATION-DIA. OF WIRE:  $d_2$  MIN.- 0.1
-  COLOUR TYPE 1: COLOUR PER FRENCH STANDARD  
DIN COLOUR TYPE: COLOUR PER DIN 46228 PART 4
- 5 NOTE DELETED
-  0.6MM ALLOWABLE MOLDING FLASH PRESENT IN THIS ZONE
-  STRIP FORM ON CARDBOARD REEL, DIA. ABOUT 450mm
-  MATERIAL:  
METAL SLEEVE - COPPER  
PLASTIC SLEEVE - POLYPROPYLENE
-  FINISH:  
METAL SLEEVE - TIN PLATE 3µm MIN THICKNESS  
PLASTIC SLEEVE COLOR - SEE TABLE

- 10 MAXIMUM RECOMMENDED TEMPERATURE 105°C
-  PARTS PER DIN 46228 PART 4 EXCEPT FOR S2 DIMENSION WHICH INCLUDES PLASTIC CARRIER STRIP CUTOFF BURR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. WERNER 29-APR-96	 TE Connectivity	
		CHK R.SCHMIDT 29-APR-96		
		APVD G.FELDMEIER 12-SEP-00	NAME	
		PRODUCT SPEC	WIRE FERRULE WITH PLASTIC SLEEVE, SINGLE CONDUCTOR, DIN 46228 PART 4, STRIP & REEL FORM DIN & FRENCH COLOR CODING	
		APPLICATION SPEC	SIZE	CAGE CODE
		WEIGHT	A3	00779
		CUSTOMER DRAWING	DRAWING NO	RESTRICTED TO
			C-966903	
		SCALE	SHEET	REV
		-	1 OF 1	E