

REV. 0

DCO 142552

COIL: @ 25°C	
RESISTANCE	4000 OHMS ±10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	15.4 VDC
MUST RELEASE	8.0 VDC MAX, 1.37 VDC MIN.


ENVIRONMENT:

VIBRATION	10	CPS TO	3000	CPS @	30	g's
SHOCK	75	g's	6	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

NOTES:

OPERATE TIME	4.0 MS MAX
RELEASE TIME	7.5 MS MAX
CONTACT BOUNCE	15 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. PBB 12/12/00

CK. 12/12/00

CII Technologies
advanced control electronic solutions

CUST. OPL
CUST. NO. M39016/26-044L REV. _____

'J1MSDD' RELAY

J1MSCDD-26XLS