




# CATALOGUE NUMBER: FAD2020-2185-8 SUITS CONDUCTOR

**DEADEND**

STRANDING/CONDUCTOR	COND. TYPE	DIAMETER	FITTING LAY
37/3.00	AAC/AAAC	21.00	RIGHT HAND
19/0.166	AAC/AAAC	21.08	RIGHT HAND
COVERED CONDUCTOR XPLE	AAC/AAAC	20.20-21.85	RIGHT HAND
CCT 120mm2	AAC/AAAC	20.90-22.40	RIGHT HAND



### TECHNICAL SPECIFICATIONS:

**CATALOGUE NUMBER:** FAD2020-2185-8  
**DESCRIPTION:** FULL-TENSION ALUMINIUM DEADEND  
**MATERIAL:** ALUMINIUM ALLOY  
**NUMBER OF RODS:** 6  
**ROD DIAMETER:** 5.40mm  
**OVERAL LENGTH:** 1350mm  
**END FINISH:** BALLENDED  
**FITTING LAY DIRECTION:** RIGHT HAND  
**COLOUR CODED:** RED

### BOX LABEL

**P/N:** FAD2020-2185-8  
**ID:**  
**DESCRIPTION:**  
**FULL-TENSION ALUMINIUM DEADEND**  
 37/3.00 & 19/0.166 AAC/AAAC  
 CCT 120mm2 20.90-22.40  
 XLPE 20.20-21.85  
**RANGE:** 20.20 - 21.85  
**COLOUR-CODE:** RED  
**QTY:** 10    **WEIGHT:** .....    **BATCH:** .....

### PRODUCT LABEL

**FAD2020-2185-8**  
 37/3.00 & 19/0.166 AAC/AAAC  
 CCT 120mm2 20.90-22.40  
 XLPE 20.20-21.85

**WEIGHT:** 1.16kg  
**BATCH NO:** .....  
**MONTH/YEAR:** .....

LOC	IMPLIED NOTES			IMPLIED TOLERANCES			TCPN	TITLE		
	BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE			HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm: ±1.5mm. DIMENSIONS OVER 30mm: ±5%. UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5°			-	FULL-TENSION ALUMINIUM DEADEND (FAD) FITTING COND. RANGE: Ø 20.20-Ø 21.85    37/3.00 & 19/0.166 AAC/AAAC CCT 120mm2 20.90-22.40 & XLPE 20.20-21.85		
DIST	NEW RELEASE			15-05-2013			RN	DRAWN: RN    DATE: 15-05-2013 CHECKED: MN    APPROVED: AT		
POS	REV	REVISION RECORD		DATE	DWN	APVD	MATERIAL DESC: ALUMINIUM ALLOY MATERIAL NO: -    MATL SPEC/STD/DRG NO: -    PROCESS SPEC HEAT TREAT/PLATING NO: -			
						SIZE: A3    PROJECTION: 3RD ANGLE    SCALE: NTS DRAWING NO: FAD2020-2185-8-C    SHEET: 1 OF 1    REV: 1				