


COIL: @ 25°C  
 RESISTANCE 100 OHMS ± 10%  
 NOMINAL VOLTAGE 5.0 VDC  
 MUST OPERATE 3.5 VDC  
 MUST RELEASE 1.7 VDC MAX, 0.23 VDC MIN.

ENVIRONMENT:  
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX.  
RELEASE TIME 7.5 MS MAX.  
CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 2/6/98 *CK JERRY C 2/6/98*



CUST. QPL  
 CUST. NO. M39016/26-033L

TYPE J1MSDD RELAY

**J1MSCDD-5XL**