
WEIGHT:

CATALOGUE NUMBER: NCA1785-1870 SUITS CONDUCTOR

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
37/0.103	COPPER	18.31	RIGHT HAND



BOX LABEL



P/N: NCA1785-1870

ID:

DESCRIPTION:

NON-TENSION HARD DRAWN COPPER ARMOUR RODS 37/0.103 COPPER

WRAPTER

ARMOUR RODS

RANGE: 17.85 - 18.70 COLOUR-CODE: BLUE

BATCH:

PRODUCT LABEL



= TE WEIGHT: 3.18kg BATCH NO: MONTH/YEAR: ..

TECHNICAL SPECIFICATIONS;

CATALOGUE NUMBER: NCA1785-1870

DESCRIPTION: NON-TENSION HARD DRAWN COPPER ARMOUR RODS

MATERIAL: HARD DRAWN COPPER WIRE

NUMBER OF RODS: 13 **ROD DIAMETER: 4.47mm** OVERAL LENGTH: 1625mm END FINISH: CHAMFERED

FITTING LAY DIRECTION: RIGHT HAND

COLOUR CODED: BLUE

RODS ARE LABELED, BUNDLED IN A SET AND TAPED AT BOTH ENDS.

						BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE UP TO A MAX OF	.5-1870 COND.RANGE: Ø17.85-Ø18.70 37/0.103 COPPER DRAWN DATE
_	I NEW RELEASE		06-05-2013	RN	ΑТ	MATERIAL DESC HARD DRAWN COPPER WIRE	CHECKED APPROVED APPROVED Berkeley Vale NSW 2261
POS R	REV	REVISION RECORD	DATE	DWN	APVD	MATERIAL NO MATE SPEC/STD/DRG NO PROCESS SPEC HEAT TREAT/PLAT	ING NO SIZE PROJECTION SCALE DRAWING NO SHEET OF NCA1785-1870-C I