


REV. 0  
DCO 143764

COIL: @ 25°C	
RESISTANCE	1560 OHMS ±10%
NOMINAL VOLTAGE	26.5 VDC
MUST OPERATE	14.2 VDC
MUST RELEASE	8.0 VDC MAX., 1.37 VDC MIN.

ENVIRONMENT:	
VIBRATION	10 Hz TO 3000 Hz @ 30 g's
SHOCK	75 g's 6 MS. DURATION
TEMPERATURE	-65 °C TO +125 °C

NOTES:	OPERATE TIME 2.0 MS MAX.
	RELEASE TIME 1.5 MS MAX.
	CONTACT STABILIZATION 2.5 MS MAX.

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING:	LOW LEVEL TO 1 AMP
	28 VDC RESISTIVE 100,000 OPERATIONS

DR. B.D. 11JUL03 *CK JERRA 7/14/03*

**CII Technologies™**  
advanced control electronic solutions

CUST. QPL  
CUST. NO. M39016/17-042M REV.

"JMGA" RELAY

JMGAC-26MW