





THIS DRAWING IS UNPUBLISHED
 RELEASED FOR PUBLICATION 2016
 © COPYRIGHT 1999 BY TE CONNECTIVITY ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
C		REVISED PER PCN-23-192205	11APR2024	PS	CB
G		REVISED PER PCN-24-210155	09SEP2024	AJ	CB



- 4. RESISTOR CHARACTERISTICS: 120 OHMS±10 PERCENT, .4 WATTS MINIMUM INSERTED INTO CAVITIES A AND B.
- 3. THIS CONNECTOR CAN PASS THRU A ONE INCH [25.44] HOLE.

2 MATERIAL: HOUSING:PA66 GF15, (GRAY)
 CAP: PA66 GF15, (BLACK)
 GROMMET: VMQ (RED-ORANGE)
 FRONT SEAL: VMQ (RED-ORANGE)
 WEDGE LOCK: PBT GF30 (BLUE)
 SOCKET TERMINAL: COPPER ALLOY; GOLD PLATED

1. THIS PLUG MATES WITH THE DT04-3P-XXXX RECEPTACLE.
 (XXXX = J1939 MODIFICATIONS.)
 CONSULT FACTORY FOR MODIFICATIONS.
 SECONDARY WEDGE LOCK W3S-1939-P012 IS KEYED AND INCLUDED TO PREVENT MISMATING AND MAY NOT MATE WITH ALL 3 WAY DT SERIES RECEPTACLES.

NOTES:

TE INTERNAL PN	DEUTSCH PN
DT06-3S-P006	DT06-3S-P006

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	S. THEIS	08JUL1999	 TE Connectivity	NAME 3 WAY PLUG DT SERIES (TERMINATING PLUG), P006 MOD
DIMENSIONS: in [mm]		CHK	V. TOMSA	08MAY2000		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	R. READ	10MAY2000		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±°		PRODUCT SPEC	108-151009			
MATERIAL	FINISH	APPLICATION SPEC	114-151009		SIZE	A3
2		WEIGHT	8.00g		CAGE CODE	4AFU8
CUSTOMER DRAWING			DRAWING NO		C=DT06-3S-P006	
			SCALE	3:1	SHEET	1 OF 1
			REV		G	

printed on 10 Sep 2024 13:28 (Eastern Standard Time) from TE354946